

FREERPORT ILLINOIS, U.S.A
A DIVISION OF HONEYWELL
FED. MFG. CODE 91929

CATALOG LISTING

YE-2RV198-A41

SWITCH-BASIC

YE-2RV198-A 41

REPLACES X73400-YE

RELEASE NO. PR-11447

N

**DRAWING
NUMBER**

LC

193UE

REVISIONS

A C080986

JALA
11 JUN 95

B	0000782
---	---------

JAH
8 JUL 03

CHECK

CHECK

28

Aug

22	1
----	---

35

CHECK K


6 82

17 AUG

AG

RASTER

DRAWN




NOTES

- ① MOUNTING HOLES WILL ACCEPT PINS OR SCREWS
OF .139 MAX DIA ON 1.000±.002 CENTERS
2 - LEVER (1), AND PIN (1) FURNISHED UNASSEMBLED

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



OPERATING FORCE ----- 15-21 OZ
RELEASE FORCE ----- 10-14 OZ
PRETRAVEL----- .050 MAX
DIFFERENTIAL TRAVEL---.0020-.0075
OVERTRAVEL ----- .010 MIN

CONTACT ARRANGEMENT

S P N O

25A-125, 250, 480 VAC
1 HP-125 VAC; 2 HP-250 OR 480 VAC
PILOT DUTY 750 VA-480 VAC, MAX
60/75°C (Cu)



SCALE FULL

DO NOT SCALE PRINT

TOLERANCES

APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR
REFERENCE. UNLESS NOTED, TOLERANCES ARE $\pm$

	DIM. mm	TOL. mm/in	DIM. in	TOL. mm/in
NO PLACES	X	1/.04		
ONE PLACE	X, X	0.4/.016	X, X	0.8/.03
TWO PLACES	X, XX	0.18/.008	X, XX	0.38/.016
THREE PLACES			X, XXX	0.13/.005

DESIGN UNITS ☐ METRIC

US CUSTOMARY
☒

WEIGHT