

[→ Honeywell.com](#) [→ Automation & Control Solutions](#)[HOME](#)[ABOUT US](#)[KEY INDUSTRIES SERVED](#)[PRODUCTS & INFORMATION](#)[NEWS & EVENTS](#)[SALES & SUPPORT](#)[LOGIN](#)

## Honeywell Sensing and Control

Search

**11TL1-1**

( Home : Products : Switches » MICRO SWITCH™ Toggle Switches » TL )


### narrow your search

#### Products

- Controls Monitoring and Lighting (352)
- Machine Safety (1727)
- Sensors (5901)
- Switches (9775)
- Wireless (39)

#### Technology

- Control and Instrumentation (1052)
- Electromechanical (9301)
- Magnetic (541)
- Microstructure (1492)
- Thick Film (1409)



*Actual product appearance may vary.*

TL Series Toggle Switch, 1 pole, 3 position, Solder terminal, Standard Lever, Military Part Number MS27734-21

[Sales & Service](#)[Distributor Inventory](#)

### contacts

Customer Service  
Technical Support  
Global Sales & Service  
View Site Demo  
Site Comments?

### meet dr. larry

**VIDEO** - Dr. Larry Goldstein explains our newest and best technologies.

Meet Dr. Larry



### my links

Login to iCOM  
Login to Rep/AD Portal  
Login to Digital University

### News Center

HONEYWELL ANNOUNCES ADDITION TO RELIALIGN™ RESIDENTIAL DOOR INTERLOCK SWITCHES THAT FEATURE RUGGED, PLASTIC HOUSING

HONEYWELL RELEASES UNLIMITED POTENTIAL WITH NEW LIMITLESS™ WIRELESS SWITCHES

HONEYWELL'S XYR6000 WIRELESS POSITION SENSOR ENABLES MONITORING IN HAZARDOUS AREAS AND REMOTE LOCATIONS

**MICRO SWITCH Anniversary site**

### new products

#### New Wireless Products

Go farther. Work smarter. Explore new possibilities. Just by cutting the cord and making the switch.



Wireless Web Site  
WGLA and WPMM  
XYR6000™

[find out more](#)

### white papers

Wireless Switches Offer Unlimited Benefit  
Basic Switches Are Not Created Equal  
Applying Precision Switches  
Sensors for Medical Devices  
New Ways to Measure Torque  
Choosing Safety Switches  
Specifying Hour Meters


### Need help?

[Click here to contact us](#)

[Overview](#) [Specs](#) [Documentation](#) [Application Notes](#)

#### Product Specifications

Circuitry/Operating action



Product Type

MICRO SWITCH™ Toggle Switch

Ampere/Voltage Range (Resistive Load)

0.75 A at 115 Vdc, 0.5 A to 20 A at 0.5 Vdc to 28 Vdc, 0.5 A at 250 Vdc, 0.5 A to 15 A at 0.5 Vac to 277 Vac

Circuitry

SPDT

Action

3 position

Mounting

Bushing 15/32 in

Termination

Solder

MIL Spec. Number

MS27734-21

Lever Type

Standard

UL/CSA

L191: 15 A-125, 250, 277 Vac; 1/2 Hp-125 Vac; 1 Hp-250, 277 Vac; 5 A-120 Vac "L"

Comment

Single turret solder lug termination

Availability

Global

UNSPSC Code

30211908

UNSPSC Commodity

30211908 Toggle switches

Series Name

TL

[Terms & Conditions](#) | [Privacy Statement](#) | [Site Map](#)