


T 3649 501 U



Data Overview

Description:	Male Coupling Plug; 14a Pin; Solder; Silver; 4-6mm; IP40
rated voltage	150 V
number of positions (w/o PE)	14
rated current (40 °C)	3 A
termination	solder pin
contact plating	silver
IP-class mated	IP40
Product Availability	Currently not on stock
Packing Unit:	50 Pieces
Min. Order Quantity:	50 Pieces

Price per Piece: **€5.47**
Total Price plus VAT: **€273.50**

[Send Request](#) ✉

50

Add to Cart

[Stock of our Distributors](#) ▾

Technical Data

General Characteristics	+
part category	coupling connector
gender	male
locking system	bayonet ring
housing style	straight
minimum cable diameter	4 MM
maximum cable diameter	6 MM
lower temperature	-40 GC
upper temperature	100 GC
IP-class mated	IP40
Electrical Characteristics	+
Further Characteristics	+
Downloads	+

Frequently Asked Questions

Which components belong to a complete bill of materials (BOM)?	+
Amphenol as a supplier of complete assemblies and plug & play solutions	+
What options are there for direct transfer to a printed circuit board?	+
How does the transmission of the cable shielding work with M16B connectors?	+
Crimping or soldering - what are pros & cons?	+
Tarnishing of silver-plated contacts - what's the reason?	+
What options are there for color adjustments to the application?	+
M16 receptacles with hex nut instead of ring nut?	+
What are the 5 and 7 pole stereo layouts used for?	+
What does the U at the end of the part number stand for?	+

This might interest you

Accessory »

Housing »

Disclaimer: No liability is accepted for the correctness and completeness of the suggested accessories.

- Contact
- Downloads
- Imprint
- General Conditions
- Career
- Privacy Policy
- Privacy Settings



Newsletter

E-Mail

☐ I would like to receive the newsletter on the latest products, current trade fairs and promotions and give the following [consent](#).

Subscribe to Newsletter