

Precautions for use

General notes

T-375-12

made in JAPAN



Add to My List >

Sample request (Only available in Japan) >

Order model number

Order model number	T-375-12-[Body color]
Order example	T-375-12-R (An example of an order with a red color.)

Basic information

Dimension

Soldering heat resistance conditions

Download

Body color



Basic information

Rating	125V-10A
Insulation resistance	DC500V、100MΩ Min
Withstand voltage	AC1000V (1minute)
How to mount	With nut
Nut torque	0.8N・m Max
Main insulator	Polycarbonate
Body color	R (Red)、B (Black)
Note	Knob removal: Possible

Home

Product search

Product Category

About SATO PARTS

News classification

Contact us

Video channel

Download brochure

Environmental initiatives

Privacy policy

Download terms

Terms of Use