



Emergency Stop FF01 Series **FF01-26BBRAYG3**



*The photo is a sample image.
The color and shape may differ from the actual product.
*Please be sure to check the actual color and shape with a product sample.

 3D CAD

 PDF

Product Introduction

Compact Emergency Stop Push Button Switch (FF01 Series) - Solder Terminal Type - 2-Pole Single Throw - Arrow Indicator - $\Phi 30$ - Function: Locking Type (Push Lock, Pull or Turn Reset) - Panel Seal Mechanism - IP65 - UL/TUV Certified - Operating Temperature Range: -25 to 60° C - Applications: Small Wireless Control Panels, Teaching Pendants, Portable Devices, Handheld Devices - EU-RoHS Compliant - Model Number: FF01-26BBRAYG3

Product overview

Model Name	FF01-26BBRAYG3
category	emergency stop
series	FF01
Subcategory	Non-illuminated switch
Current capacity for detailed display1	0.5A DC24V
Operating temperature range (° C)	-25/+60
Number of poles	2 poles
Function 1	ON-OFF
Function 2	rock
Operation part shape	30
Terminal shape	Solder terminals
Environmental performance	RoHS

Functionality-enhancing accessories

- ▶ Jig AT-119
- ▶ Switchguard AT-220 (Switchguard - Yellow)
- ▶ Nameplate AT-221 (Nameplate - Yellow)
- ▶ Nameplate AT-222 (Nameplate - Yellow)
- ▶ Nameplate AT-223 (Nameplate - Yellow)
- ▶ Nameplate AT-224 (Nameplate - Yellow)

Total 6 items

Back to Series TOP