

## Product Line

DeepTronica

>

Single Pair Ethernet

>

ZConnect

>

Ceres

>

X-Lok

>

- Accessory
- Middle Size
- Mini Size
- Large Size
- Standard Size

M Series

>

FLOS & FLOS+

>

Power

>

RBL

>

HS-Lok

>

NMEA 2000

>

Heavy Duty Shielded

>

RJ

>

USB

>

SSL

>

HDMI

>

DVI

>

Fiber Optic

>

RF

>

Cable Joiner

>

Cable Gland

>

Pressure Relief Vent

>

LED Light Guide

>

D-Sub

>



## BB-02BFMA-QL8MPP

- Operating Temperature: -40°C ~ +105°C
- Transmission Speed: N/A
- Shielded: Plastic, Non-shielded
- Jacket Material: N/A
- Certificate: UL1977

You must login first for view the price

Quantity

-

1

+

Check Stock

Add to Cart

Inquiry



Can't find? [Customize your part](#)

## Mating Pair & Accessories

Connector Type

Search

X-Lok, Standard...  
AB-BB02FL-BBHL...  
-20°C ~ +80°C

- 0 +

X-Lok, Standard...  
AB-BB02FL-BBHL...  
-20°C ~ +80°C

- 0 +

X-Lok, Standard...  
AB-BB02FL-BBHL...  
-20°C ~ +80°C

- 0 +

X-Lok, Standard...  
AB-BB02FL-BBHL...  
-20°C ~ +80°C

- 0 +

X-Lok, Standard...  
AB-BB02FL-BBHL...  
-20°C ~ +80°C

- 0 +

X-Lok, Standard...  
AB-BB02FL-BBHL...  
-20°C ~ +80°C

- 0 +

Add to Cart

Inquiry

| Specifications                     | Download / CAD                      |
|------------------------------------|-------------------------------------|
| Nominal Current<br>10A             | Connector Type<br>Field Installable |
| Shielded<br>Plastic, Non-shielded  | No. of Contacts<br>02               |
| Connector Gender<br>Female         | Backshell<br>Straight               |
| Mating Style<br>Push Lock          | IP Rating<br>IP68                   |
| Assembly Style<br>Crimp            |                                     |
| <div><div></div>More Options</div> |                                     |

## People Also Bought

BB-02BFMA-QL8MPP

AB-DC02FR-DCBR-...

M12A04MR-12AMR-...

B-03PFFS-SH7A30

M12A-10BFFM-...

ABOUT AMPHENOL LTW

SUPPORT

PARTNERS

DOWNLOAD CENTER

FEEDBACK

Downloaded from Arrow.com