


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	11/5/14	D.GRIFFIN
B	ECN 7679: ADDED COLOR CHART	11/14/14	D.FRISIELLO



SPECIFICATIONS:

INSERTION LOSS: <0.2dB
DURABILITY 500 MATINGS: <0.2dB
OPERATION TEMPERATURE: -40 °C~+75 °C
STORAGE TEMPERATURE: -40 °C~+85 °C


MISCELLANEOUS:

THIS COMPONENT WILL SHIP IN THE KEY UP TO KEY DOWN CONFIGURATION.
POLARIZATION KEY ALLOWS KEYWAY CHANGE EASILY.
RECOMMENDED PANEL THICKNESS .062 MAX.
DUST CAPS INSTALLED FOR SHIPPING (NOT SHOWN).
COMPONENT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:

CE2011/65/EU(RoHS DIRECTIVE)

MODEL NUMBER	COLOR
FOA-MPOF	AQUA
FOA-MPOFB	BLACK

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5.08] .XX = ±.02 [51] .XXX = ±.005 [13] PROJECTION 	APPROVALS	DATE	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845		CATEGORY	PRODUCT DESCRIPTION	SIZE A	FSCM NO. 43321	DWG. NO. FOA-MPOF	REV. B
	DRAWN BY D. CASTRO	11/4/14								
	CHECKED BY D. GUITADAURO	11/5/14	FIBER OPTICS							
	APPROVED BY D. GALLAGHER	11/5/14	MPO COUPLER W/ FLANGE, KEYWAY CONVERTIBLE							
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		COLOR VARIATIONS MAY OCCUR		SCALE: NONE		CAD FILE: FOA-MPOF.SLDRW		SHEET 1 OF 1		