



HOME



会社概要

環境に対する
取り組みカタログ・サンプル
STEPファイル請求

問い合わせ

We contribute to manufacturing with delivery time, quality, and service.

Employment Information

Site Map

E-Mail: marketing@satoparts.co.jp

Model number search

Search

Model number search
within category

Search

[Refine search]

Pitch order


- | | |
|---------------------------------|---------------------------------|
| ☐ 2.54mm | ☐ 3.5mm |
| ☐ 3.81mm | ☐ 5mm |
| ☐ 5.08mm | ☐ 6.9mm |
| ☐ 7.5mm | ☐ 7.62mm |
| ☐ 8mm | ☐ 9mm |
| ☐ 9.2mm | ☐ 10mm |

By application / shape

- ☐ 2-piece terminal block
- ☐ 2-stage terminal block
- ☐ Option plate

[home](#) > [List of screwless terminal blocks](#) > SL-4000-CWJV

SL-4000-CWJV

This product is a substitute for [ML-4000-CWJV](#).

made in Japan

Pitch between terminals 3.81 mm

2-piece terminal block

Wide variation

[Information on the RoHS Directive](#)[R 50270956](#)

* Icon link, overseas standard certificate

specification

[Product Summary](#) / [specification](#) / [Dimensional drawing](#) / [Dimension table](#) / [Order model number](#) /

[Solder heat resistance conditions](#) / [Optional Accessories](#) / [download](#)

Request STEP files and samples of the product you are currently





HOME



会社概要

環境に対する
取り組みカタログ・サンプル
STEPファイル請求

問い合わせ

☐ Mounting rail☐ For relay

Rated V

☐ 50V ☐ 150V☐ 250V ☐ 300V☐ DC300V

Rating A

☐ 3A ☐ 5A☐ 7A ☐ 10A☐ 15A ☐ 20A

By acquisition standard

☐ CSA ☐ C-UL☐ PSE-JET ☐ TUV☐ UL

Search for

Acquisition standard

UL standard, C-UL standard, TÜV standard (IEC61984)

Number of poles (P)

2, 3, 4, 5, 8, 10, 12

Main insulation material
(receptacle body)

Nylon 66 (UL94V-0)

Terminal bracket

PC terminal

Body color

GY (gray)

Product Summary

(1) [SL-4000-CWSV](#) is a product only on the receptacle side.

Precautions for use

(1) When using as a standard product, check the restrictions on the standard. (2) When used as a set with a plug, it is recognized as a UL or C-UL product.

Dimensional drawing

Supplementary information (PDF)

▶ Handling precautions







▶ General notes



スクリーレス端子台

[Product Summary](#) / [specification](#) / [Dimensional drawing](#) / [Dimension table](#) / [Order model number](#) / [Solder heat resistance conditions](#) / [Optional Accessories](#) / [download](#)



Request STEP files and samples of the product you are currently





販売中止品



製品一部変更



プリント基板用取付孔例



Unit: mm

Dimension table

Number of poles	B	C	Number of poles	B	C	Number of poles	B	C	Number of poles	B	C
2	8.61	3.81	Four	16.23	11.43	8	31.47	26.67	12	46.71	41.91
3	12.42	7.62	Five	20.04	15.24	Ten	39.00	34.20			

[Product Summary](#) / [specification](#) / [Dimensional drawing](#) / [Dimension table](#) / [Order model number](#) / [Solder heat resistance conditions](#) / [Optional Accessories](#) / [download](#)

Request STEP files and samples of the product you are currently



HOME



会社概要

環境に対する
取り組みカタログ・サンプル
STEPファイル請求

問い合わせ

Order example SL-4000-CWJV-2PGY (when ordering with 2P)

Solder heat resistance conditions

Flow soldering conditions

Preheating temperature	100-140 °C
Preheating time	40 seconds
Immersion temperature	265 ± 3 °C
Immersion time	10 ± 1 second

Hand soldering (soldering ironing) conditions

Iron tip temperature	350 °C
Iron guessing time	3 seconds
Number of times	Once


Precautions

[Product Summary](#) / [specification](#) / [Dimensional drawing](#) / [Dimension table](#) / [Order model number](#) /
[Solder heat resistance conditions](#) / [Optional Accessories](#) / [download](#)


Request STEP files and samples of the product you are currently



HOME



会社概要

環境に対する
取り組みカタログ・サンプル
STEPファイル請求

問い合わせ

Optional Accessories

Misinsertion prevention
mold[ML-1000-M1](#)

DXF / Environmental Impact On the Environment Report (chemSHERPA)

Download

* Please read the [DXF file terms](#) of [use](#) when downloading the [DXF file](#).

* For the Environmental Impact On the Environment Report , please see our [Environmental Initiatives](#).

* For tools for viewing chemSHERPA data, see the [PDF download procedure manual](#).

In addition, with regard to the survey list, [PDF click here](#) please refer to.

Model number	DXF file	Environmental Impact Substance Report (chemSHERPA)
SL-4000-CWJV-2PGY	download	download

[Product Summary](#) / [specification](#) / [Dimensional drawing](#) / [Dimension table](#) / [Order model number](#) /
[Solder heat resistance conditions](#) / [Optional Accessories](#) / [download](#)

Request STEP files and samples of the product you are currently

 HOME

 会社概要

 環境に対する
取り組み

 カタログ・サンプル
STEPファイル請求

 問い合わせ

SL-4000-CWJV-8PGY	download	download
SL-4000-CWJV-10PGY	download	download
SL-4000-CWJV-12PGY	download	download

[HOME](#) | [Company Profile](#) | [Terms of use](#) | [privacy policy](#) | [site map](#)

COPYRIGHT © SATO PARTS CO., LTD. ALL RIGHTS RESERVED.

SATO PARTS Co.
, Ltd.
Akihabara Building , 3-3-8 Sotokanda, Chiyoda-ku, Tokyo 101-0021

[Product Summary](#) / [specification](#) / [Dimensional drawing](#) / [Dimension table](#) / [Order model number](#) / [Solder heat resistance conditions](#) / [Optional Accessories](#) / [download](#)

Request STEP files and samples of the product you are currently