


Type 4 Mild Steel Wallmount Enclosure w/ Window *Eclipse Series*

Hinge Door with Quarter Turn



**Panel
Sold
Separately**



Application

- Designed to enclose electrical and/or electronic equipment in wallmount applications where viewing of component operation is necessary while maintaining protection ratings.
- Impressive styling features like hidden hinges, attractive latching systems make the Eclipse a suitable addition to any high-tech equipment installation.
- A wide range of sizes and practical accessories make this product line a complete package.

Standards

- UL 508A Type 3R, 4 and 12
- CSA Type 3R, 4 and 12
- Complies with
 - NEMA 3R, 4 and 12
 - IEC 60529, IP66

Construction

- Formed 14 (24x24" and larger) or 16 (24x20" and smaller) gauge steel.
- Full view UV resistant polycarbonate window allow maximum viewing area of inner panel.
- Smooth, continuously welded seams ground smooth.
- Door stiffeners are provided where required for increased strength and rigidity - designed to also permit additional mounting options.
- Formed lip on enclosure to exclude flowing liquids and contaminants.
- Door latches feature the added safety of quarter turn slot requiring use of tool for opening.
- Doors may be easily removed for modifications and are interchangeable.
- Seamless poured-in place gasket.
- Collar studs provided for mounting inner panel.
- Includes hardware kit with panel mounting nuts and sealing washers for wall mounting holes.
- Bonding stud provided on door and grounding stud installed in enclosure.
- Hinges are constructed from 304 stainless steel.
- Hinge pins are stainless steel.
- Quarter turn latches are zinc diecast with black epoxy finish.

Finish

- Cover and enclosure are phosphatized and finished with a recoatable powder inside and out with choice of ANSI 61 smooth Gray (GY) or RAL7035 textured light gray (LG).

Accessories

- Additional Inner Panels
- Swing Panel

- Swing Frame
- Eclipse DIN Rail Mounting Kit
- Door Stop Kit
- Rear Hole Plugs
- Quarter Turn Assemblies
- Padlock Adaptor
- Replacement Hinge Pins
- Climate Control
- General Accessories
- Rack Rail Mounting Panel for Eclipse Enclosures
- Eclipse DIN Rails
- Mounting Foot Kit
- Drip Shield Kit
- Quarter Turn Inserts and Keys
- Handles
- Window Kits
- Lighting

New and improved PDF part drawing files with more detail now available.

Click part number in table below to access PDF, DXF, and STEP files.

ANSI 61 Gray Part No.	RAL7035 Light Gray Part No.	H	Enclosure W	D	Optional Inner Panel Part No.	H	W
EN4SD16126W GY	EN4SD16126W LG	16.00	12.00	6.00	EP1612	14.20	10.20
EN4SD20166W GY	EN4SD20166W LG	20.00	16.00	6.00	EP2016	18.20	14.20
EN4SD20206W GY	EN4SD20206W LG	20.00	20.00	6.00	EP2020	18.20	18.20
EN4SD24206W GY	EN4SD24206W LG	24.00	20.00	6.00	EP2420	22.20	18.20
EN4SD24246W GY	EN4SD24246W LG	24.00	24.00	6.00	EP2424	22.20	22.20
EN4SD16128W GY	EN4SD16128W LG	16.00	12.00	8.00	EP1612	14.20	10.20
EN4SD20168W GY	EN4SD20168W LG	20.00	16.00	8.00	EP2016	18.20	14.20
EN4SD20208W GY	EN4SD20208W LG	20.00	20.00	8.00	EP2020	18.20	18.20
EN4SD24208W GY	EN4SD24208W LG	24.00	20.00	8.00	EP2420	22.20	18.20
EN4SD24248W GY	EN4SD24248W LG	24.00	24.00	8.00	EP2424	22.20	22.20
EN4SD30248W GY	EN4SD30248W LG	30.00	24.00	8.00	EP3024	28.20	22.20
EN4SD202012 WGY	EN4SD202012 WLG	20.00	20.00	12.00	EP2020	18.20	18.20
EN4SD242012 WGY	EN4SD242012 WLG	24.00	20.00	12.00	EP2420	22.20	18.20
EN4SD242412 WGY	EN4SD242412 WLG	24.00	24.00	12.00	EP2424	22.20	22.20
EN4SD302412 WGY	EN4SD302412 WLG	30.00	24.00	12.00	EP3024	28.20	22.20
EN4SD242416 WGY	EN4SD242416 WLG	24.00	24.00	16.00	EP2424	22.20	22.20
EN4SD242420 WGY	EN4SD242420 WLG	24.00	24.00	20.00	EP2424	22.20	22.20
EN4SD302420 WGY	EN4SD302420 WLG	30.00	24.00	20.00	EP3024	28.20	22.20

¹ All Window Door latch types are quarter turns. Alternative inner panel options also available.

