

HK Series / Test Point for Auto Insertion


Test Point for Auto Insertion [HK-2 Series] (3.2x1.6 type) (1000pcs/reel) **PAT**

■ In the case of reflowing by cream solder, recommended mounting land diameter should be more than 1.6x3.2 to strengthen the bonding

■ Material.....Brass




■ Finish.....HK-2-GPlated Au over Ni base
HK-2-SPlated Sn over Ni base

N/O	Package
HK-2-G	1000/reel
HK-2-S	1000/reel



■ Recommended Land Diameter

■ Dimensions



Test Point for Auto Insertion [HK-3 Series] (2x1.25 type) **PAT**



■ Best use for small equipments.

■ In the case of reflowing by cream solder, recommended mounting land diameter should be more than 2x1.25 to strengthen the bonding.

■ Material.....Brass




■ Finish.....HK-3-GPlated Au over Ni base
HK-3-SPlated Sn over Ni base

N/O	Package
HK-3-G-T	1500pcs/reel
HK-3-G	1000pcs/bulk
HK-3-S-T	1500pcs/reel
HK-3-S	1000pcs/bulk



■ Recommended Land Diameter

■ Dimensions



MAC8 No.1 distributor of MAC8
SHINDENKIZAI Co., LTD.
Contact
e-mail: sdk@mac8sdk.co.jp FAX: +81-3-3253-5965



http://www.mac8sdk.co.jp/index_e.html

HK Series / Test Point for Auto Insertion


Test Point for Auto Insertion [HK-4 Series] (1.2X1.0 type)

- In the case of reflowing by cream solder, recommended mounting land diameter should be more than 1.3x1.1 to strengthen the bonding.
- Can hook oscilloscope on the hole
- Material.....Brass
- Finish.....HK-4-G..... Plated Au over Ni base
HK-4-S..... Plated Sn over Ni base


N/O	Package
HK-4-G-T	3000pcs/reel
HK-4-G	bulk 1000pcs/pack
HK-4-S-T	3000pcs/reel
HK-4-S	bulk 1000pcs/pack




Recommended Land Diameter



Dimensions



Tape




Test Point for Auto Insertion [HK-5 Series]


PAT

- In the case of reflowing by cream solder, recommended mounting land diameter should be more than 1.25x2.5 to strengthen the bonding.
- Size: 2.5x3.0
- Operating Temperature.....-40~+150°C
- Material
PinPhosphor Bronze 0.2t
Plastic PartFluorine Resin (UL94V-0)
- Finish.....HK-5-G..... Plated Au over Ni base
HK-5-S..... Plated Sn over Ni base
- Color: Black, Brown, Red, Orange, Yellow, Green, Blue, Purple, Gray, White


N/O	Package
HK-5-G□	1000/reel
HK-5-S□	1000/reel
HK-5-G-B□	Bulk 1000/pack
HK-5-S-B□	Bulk 1000/pack




Recommended Land Diameter



Dimensions



Tape



MAC8

No.1 distributor of MAC8

SHINDENKIZAI Co., LTD.

Contact

e-mail: sdk@mac8sdk.co.jp FAX: +81-3-3253-5965

http://www.mac8sdk.co.jp/index_e.html