




MATERIAL SPECIFICATIONS:

SCREWLOCK:	BRASS - C3604, NICKEL PLATED
FLAT WASHER:	STEEL, NICKEL PLATED
LOCK WASHER:	STAINLESS STEEL
NUT:	ZINC PLATED STEEL
TORQUE VALUE:	60 IN-OZ MAX RECOMMENDED
OPERATION TEMPERATURE:	-40°C to 120°C

PART NUMBER	A	B	PKG
160-000-010R031	0.187	0.312	KIT
160-000-010R032	0.187	0.312	BULK
160-000-011R031	0.187	0.625	KIT
160-000-011R032	0.187	0.625	BULK
160-000-012R031	0.250	0.156	KIT
160-000-012R032	0.250	0.156	BULK
160-000-013R031	0.197	0.197	KIT
160-000-013R032	0.197	0.197	BULK
160-000-014R031	0.197	0.236	KIT
160-000-014R032	0.197	0.236	BULK
160-000-015R031	0.197	0.323	KIT
160-000-015R032	0.197	0.323	BULK
160-000-016R031	0.197	0.433	KIT
160-000-016R032	0.197	0.433	BULK
160-000-017R031	0.197	0.520	KIT
160-000-017R032	0.197	0.520	BULK
160-000-018R031	0.197	0.669	KIT
160-000-018R032	0.197	0.669	BULK

KIT INCLUDES:
1 - 4-40 UNC-2B FEMALE SCREWLOCK
2 - 4-40 FLAT WASHERS
1 - 4-40 LOCK WASHERS
1 - 4-40 NUTS

RoHS COMPLIANT

DRAWN:
PAM JENKINS
DATE:
05/14/2005

UNITS = inch

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

NorComp

SCALE: NTS
SHEET 1 OF 1
REV 9

DWG NO. 160-000-01YR03Y