






AFCI CONFIDENTIAL

Amphenol
FCi

This document is the property of and embodies CONFIDENTIAL and PROPRIETARY information of AFCI. No part of the information shown on this document may be used in any way or disclosed to others without the written consent of AFCI. © 2016 AFCI



PC card drilling dimensions(after plating) scale:1.5
(thickness 1.60 ±0.10mm)



GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:

SEE DRAWING C01-8646-0001

PART NUMBER

D50S82C4GX00LF	D50S82C6GX00LF
200 MATING CYCLES	500 MATING CYCLES

mat'l. code SEE NOTE				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection mm	product family D-SUB			
ltr	ecn no	dr	date	tolerances unless otherwise specified			title			
H	ELX-I-18050	MP	2014-06-23	angles 0°±2°	linear	.0±0.1	DELTA-D EUROSTYLE FEMALE 50 RIGHT ANGLED PRESS FIT			
J	ELX-I-280162	DJ	2026-03-03			.00±0.1				
						.000±0.1	scale 2:1			
				dr	PESSON	1995-10-17	Amphenol FCi			
				enr	DIPU JOSEPH	2026-03-03				
				chr	GREGAR M	2026-03-03				
				appd	ALEX BABU	2026-03-03				
sheet index	revision sheet	J 1					dwg no C01-8646-0402			
							sheet 1 of 1			
							size A3			
							type Product Customer Drawing			