


SSB Series

all categories > surface mount > tapped spacer > SSB series



Tapped Spacer - SSB Series (M3,M2.6,M2)

- Can be mounted by auto-insertion system.
 - Can be attached by reflow.
 - Taping type has adsorption cap for vacuum pick. It needs to be removed after reflow.
 - Finish....Sn plating over Ni
 - Material....Brass
 - Recommended Cream Solder Thickness....150~200μ
- 3.4
- 3SSB - 2.5~3.0
 - 2.6SSB - 2.5~3.0
 - 2SSB - 2.0~3.0
- 4.4
- 3SSB - 3.5~4.0
 - 2.6SSB - 3.5~4.0
 - 2SSB - 3.5~4.0
- 5.4
- 3SSB - 4.5~5.0
 - 2.6SSB - 4.5~5.0
 - 3SSB - 4.5~5.0
- Recommended Land Diameter....
3SSB.....5.5φ
2.6SSB... 5.0φ
2SSB.....4.5φ
 - Tap....
M3 P=0.5
M2.6 P=0.45
M2 P=0.4
 - Tightening Torque....
3SSB.....3.0kg.f.cm and below
2.6SSB... 3.0kg.f.cm and below
2SSB.....1.0kg.f.cm and below

[Save To Favorites](#)
[Download Catalog](#)

[Ask a Question](#)

[Pre-Production Quote Request](#)

[Request Sample](#)

[ADD TO CART](#)

>> request quote / information | >> download specs

N/O	A	B	L	M	Package
3SSB-2.5	4.0	5.0	2.5	M3	500pcs/reel
3SSB-3.0	4.0	5.0	3.0	M3	500pcs/reel
3SSB-3.5	4.0	5.0	3.5	M3	400pcs/reel
3SSB-4.0	4.0	5.0	4.0	M3	400pcs/reel
3SSB-4.5	4.0	5.0	4.5	M3	350pcs/reel
3SSB-5.0	4.0	5.0	5.0	M3	350pcs/reel
2.6SSB-2.5	3.5	4.5	2.5	M2.6	500pcs/reel
2.6SSB-3.0	3.5	4.5	3.0	M2.6	500pcs/reel
2.6SSB-3.5	3.5	4.5	3.5	M2.6	400pcs/reel
2.6SSB-4.0	3.5	4.5	4.0	M2.6	400pcs/reel
2.6SSB-4.5	3.5	4.5	4.5	M2.6	350pcs/reel
2.6SSB-5.0	3.5	4.5	5.0	M2.6	350pcs/reel
2SSB-2.0	3.0	4.0	2.0	M2	500pcs/reel
2SSB-2.5	3.0	4.0	2.5	M2	500pcs/reel
2SSB-3.0	3.0	4.0	3.0	M2	500pcs/reel
2SSB-3.5	3.0	4.0	3.5	M2	400pcs/reel
2SSB-4.0	3.0	4.0	4.0	M2	400pcs/reel
2SSB-4.5	3.0	4.0	4.5	M2	350pcs/reel
2SSB-5.0	3.0	4.0	5.0	M2	350pcs/reel

You can order bulk type (no adsorption seal)
3SSB-3.0 -B
add -B for bulk type (100/package)

[Pre-Production Quote Request](#)

