

In order to use our website without any issues, it is necessary that you know and accept our privacy policy.

Please note that the usage of our homepage without confirming the button "Accept" is limited.

JST Deutschland GmbH takes privacy very seriously. We have adapted our guidelines to the new Data Protection Regulation DS-GVO.

Our privacy policy in German language can be found at any time linked on the footer of our homepage.

Among other subjects, you will find information about cookies and Google Analytics there.

For further questions regarding our privacy policy, our data protection officer is at your disposal.

Please note, that there is no English version of our privacy policy because it refers to a German law.

Accept



LOGIN



search 

live chat offline 

- HOME
- NEWS
- ABOUT US
- DOWNLOAD
- PRODUCTS
- PARTNER
- JST INTERNET SHOP
- SALES
- CONTACT

Products > SC04B-F35DK-GGR (LF)(AU)

← BACK



SC04B-F35DK-GGR (LF)(AU)

Description: selective AU

Header J350D 5.08 THT side ent

Specification

Raster (mm)	5,08
Steckverbinder-typ	WtB
Polzahl	4
Stromstärke (A)	11,25
Spannung (V)	600
Anschluß-Art. (THT/SMT)	THT
Querschnitt (AWG)	28-14
liegende Version	-1
gerade Version	0
waterpoof	0
einreihig	0
doppelreihig	-1
ZIF	0
non-ZIF	0

↑ UP

Products

- FOR PC BOARD
- WIRE TO WIRE
- WATERPROOF CONNECTORS
- LOOSE PIECE TERMINALS
- CHAIN TERMINALS
- CARD- AND INTERFACE CONNECTORS
- HIGH VOLTAGE SHIELDED SEALED CONNECTOR
- AUTOMOTIVE

Information

- IMPRINT
- DATA-SECURITY

