


|                          |
|--------------------------|
| HONEYWELL<br>PART NUMBER |
| 2AC97-D8                 |
| PRODUCT CODE             |
| KC-B0668                 |

| REV | DOCUMENT | CHANGED BY  | CHECK |
|-----|----------|-------------|-------|
| 4   | 0054964  | KNR 27JUL09 | CMH   |


PUSH TO OPERATE-RETURNS AUTOMATICALLY  
TO POSITION SHOWN  
PULL TO OPERATE-REMAINS IN OPERATED  
POSITION UNTIL RESET FOR AUTOMATIC  
RETURN BY NEXT FULL STROKE "PUSH"  
OPERATION

B



- NOTES:
- 1 - NOTCH IN ACTUATOR ROD WILL PERMIT .035 DISPLACEMENT BETWEEN  
END OF ROD AND HOLE IN BRACKET
  - 2 - WITH ROD IN EITHER ACTUATED POSITION, BASIC SWITCH PLUNGER  
MUST HAVE .010 MIN OVERTRAVEL AND WITH ROD IN FREE POSITION  
BASIC SWITCH PLUNGER MUST HAVE .005 MIN RELEASE TRAVEL

A



B

A

RELEASE NO. PR-15073

| CHARACTERISTICS                                                          |  | ELECTRICAL DATA                |  | DESIGN UNITS: INCH<br>TOLERANCES UNLESS NOTED:                                         |  | DRAWN KNR 27JUL09<br>CHECK SS 27JUL09                                                                                                                           |  | Honeywell                |           |                |                          |          |
|--------------------------------------------------------------------------|--|--------------------------------|--|----------------------------------------------------------------------------------------|--|-----------------------------------------------------------------------------------------------------------------------------------------------------------------|--|--------------------------|-----------|----------------|--------------------------|----------|
| TOTAL TRAVEL<br>.250 APPROX PUSH DIRECTION<br>.187 APPROX PULL DIRECTION |  | CONTACT ARRANGEMENT<br>S P N C |  | NO PLACES x ±<br>ONE PLACE .x ±<br>TWO PLACE .xx ±<br>THREE PLACE .xxx ±<br>ANGLES x ± |  | THIS DRAWING COVERS A PROPRIETARY ITEM<br>AND IS THE PROPERTY OF HONEYWELL.<br>THIS DRAWING IS NOT TO BE COPIED OR USED<br>WITHOUT THE PERMISSION OF HONEYWELL. |  | TITLE<br>ASSEMBLY-SWITCH |           |                |                          |          |
| FULLY DEPRESSED FORCE - 4LB MAX                                          |  | 5A 1/10HP 125 OR 250 VAC       |  | THIRD ANGLE PROJECTION                                                                 |  | INTERPRET PER ANSI Y14.5M-1982<br>OTHER HONEYWELL ENGINEERING<br>STANDARDS MAY APPLY                                                                            |  | SIZE<br>B                | TYPE<br>I | CAGE CODE<br>- | DRAWING NAME<br>2AC97-D8 | REV<br>4 |
|                                                                          |  |                                |  |                                                                                        |  | Pro/ENGINEER 3D                                                                                                                                                 |  | SCALE<br>2:1             |           |                | SHEET<br>1 OF 1          |          |