


Horizontal type die-cast material backshell for larger diameter cables with provision for preventing misinsertion PCS-E()WKP()-()

1.27 mm pitch connectors

For Backshell

Horizontal

EMI-filtered






● Configuration of product Part No.

PCS-E () WKP ()-()

① ② ③ ④ ⑤

- ① Series name
- ② No. of contacts: 36, 50, 68, 80
- ③ Type of backshell
WKP: Horizontal type backshell for larger diameter cables with mating guide for preventing misinsertion

- ④ Identification mark (A or B) of cable-end-outlet dimension. Cable diameters for reference purposes are shown in the Dimension table as shown below.
- ⑤ Key-riveted position (Refer to the Dimension table as shown below) for preventing misinsertion.



● Components

①	Cable clamp
②	⊕Small-sized Phillips head screw
③	Latch
④	Cover B
⑤	Cover A
⑥	⊕Small-sized Phillips flat head screw
⑦	Key rivet

● Dimensions

Part No.	A	B	Outside diameter of cable for reference purposes	Key-riveted position No.
PCS-E36WKPA-()	40.2	10.5×9.5	ø9.5	1D, 2C, 3B, 4A
PCS-E50WKPB-()	48.9	12×10	ø11.5	1E, 2D, 4B, 5A
PCS-E68WKPA-()	60.3	11×10	ø10.5	
PCS-E80WKPA-()	67.9	10.5×9.5	ø9.5	

For use with connector: PCS-E series of IDC type female connectors for cables

PCS-E series of Soldering type female connectors for cables

PCS-XE series of IDC type male connectors for cables

Accessories: Key-rivets for preventing misinsertion, PCS-E-PK