


We recommend you print this page




Schroff
PropacPRO, Case, Unshielded, Desktop

Catalog Number: 14576-021

- Unshielded
- Prepared for GND/earthing
- Desk-top case with pre-configured components, in accordance with IEC 60297-3-101; prepared for 19" components such as plug-in units and euroboards
- Ventilation slots in base plate



Other Views



Description

Family:

PropacPRO

EMC Shielding:

- Retrofitable
- Unshielded

Options:

Front Trim

Disposition:

Case only

Type:

Case Kit


Note:

Case, 2 U with side panel for tip-up carrying handle on request


Delivery Comprises:

Item	Quantity	Description
------	----------	-------------


Item	Quantity	Description
1	1	Frame, Al die-cast, powder-coated, RAL 7016
2	2	Side panel, Al extrusion, powder-coated, RAL 9006
3	1	Cover plate, Al, 1 mm, internal surface conductive, visible surface powder-coated, RAL 9006, with GND/earthing tag
4	1	Base plate, Al, 1 mm, internal surface conductive, visible surface powder-coated, RAL 9006, with GND/earthing tag, base plate with 4 rows of ventilation slots
5	2	End piece for rear, ABS, RAL 7016, UL 94 V-0; can be used as a foot for use in vertical position
6	4	Case foot with anti-slip protection, PC, black, UL 94 V-0
7	1	Assembly kit




Cross-section 2 U, 3 U



Mounting position
horizontal/central rail



Extruded side panel



2 U

Technical Data

Catalog Number	14576-021
Qty	1 piece
Depth D mm	266.0
Height U	2
Width HP	42

Technical Data

Maximum mounting depth	D - 45 (open space: front panel - rear panel)
------------------------	---

Documents



Main Catalog - PropacPRO



User manual



Earthing instructions



EMC test report with perforated rear panel



EMC testreport (Rear panel without perforation)

Links



Native CAD files

No accessories available.

Print

Close

We recommend you print this page