

Accessories for Strain Relief Fittings Summary

 Locking Nuts - Page 28 - Black & Gray Nylon - Nickel Plated Brass	Page 29 - Locking Nuts - EMI/RFI Proof (Nickel Plated Brass) - Zinc Plated Steel - Stainless Steel (303) - INOX 
 O-Rings - Page 30 - Buna-N - FPM - Silicone	Page 30 - Seal Rings - Polyethylene - Fiber-Reinforced Plastic 
 Hole Plug - Page 31-32 Dome Plugs: - Black & Gray Nylon - Nickel Plated Brass Hex Plugs: - Black Nylon - Nickel Plated Brass - Stainless Steel	Page 30/33 - Blind Plug/Clamp Blind Plugs: - Black Nylon Cable Clamp: - Nickel Plated Brass 
 Wrenches - Page 33 Deep Socket Wrenches	Page 34-35 - Thread Adapters Converts a Type of (NPT, PG, Metric) Threads - Black Nylon - Nickel Plated Brass 
 Thread Reducers - Page 36-38 Reduces a Type of (NPT, PG, Metric) Thread - Gray Nylon - Nickel Plated Brass - Black Nylon - Stainless Steel	Page 39 - Thread Enlargers Enlarges a Type of (NPT, PG, Metric) Threads - Black Nylon - Nickel Plated Brass 

Accessories - Locking Nuts Nylon & Nickel Plated Brass - PG/NPT/Metric




Nylon: Black & Gray Locking Nuts*

Part Numbers		Thread Type & Size	Dimensions in Inches (mm)	
-40 °F to 212 °F (-40 °C to 100 °C)			G	H
			Thickness	Wrench Flats
Black	Gray	See page 49 for thread specs		
NP-07-BK	NP-07-GY	PG 7	.20 (5)	.75 (19)
NP-09-BK	NP-09-GY	PG 9	.20 (5)	.87 (22)
NP-11-BK	NP-11-GY	PG 11	.20 (5)	.94 (24)
NP-13-BK	NP-13-GY	PG 13 / 13.5	.24 (6)	1.06 (27)
NP-16-BK	NP-16-GY	PG 16	.24 (6)	1.18 (30)
NP-21-BK	NP-21-GY	PG 21	.28 (7)	1.41 (36)
NP-29-BK	NP-29-GY	PG 29	.28 (7)	1.81 (46)
NP-36-BK	NP-36-GY	PG 36	.31 (8)	2.36 (60)
NP-42-BK	NP-42-GY	PG 42	.31 (8)	2.56 (65)
NP-48-BK	NP-48-GY	PG 48	.31 (8)	2.76 (70)
NN-09-BK	NN- -GY	3/8" NPT	.28 (7)	.94 (24)
NN-13-BK	NN-13-GY	1/2" NPT	.24 (6)	1.06 (27)
NN-21-BK	NN-21-GY	3/4" NPT	.28 (7)	1.26 (32)
NN-29-BK	NN-29-GY	1" NPT	.28 (7)	1.57 (40)
NM-12-BK	NM-12-GY	M12 x 1.5	.20 (5)	.67 (17)
NM-16-BK	NM-16-GY	M16 x 1.5	.20 (5)	.87 (22)
NM-20-BK	NM-20-GY	M20 x 1.5	.24 (6)	1.06 (27)
NM-25-BK	NM-25-GY	M25 x 1.5	.26 (6.5)	1.26 (32)
NM-32-BK	NM-32-GY	M32 x 1.5	.28 (7)	1.61 (41)
NM-40-BK	NM-40-GY	M40 x 1.5	.28 (7)	1.97 (50)
NM-50-BK	NM-50-GY	M50 x 1.5	.31 (8)	2.36 (60)
NM-63-BK	NM-63-GY	M63 x 1.5	.31 (8)	2.95 (75)




Nylon Locking Nuts



Nickel Plated Brass Locking Nuts



Nickel Plated Brass Locking Nuts



* V0 Rated

Additional: Nickel Plated Brass Extra Small & Large Locking Nuts are available in Metric: (M6, M8, M10, M63, M75, M80, M90, M100, M110) & BSPP: (G 2-1/2", G 3", G 4")(See Page 15)

Nickel Plated Brass: Locking Nuts

Part Numbers		Thread Type & Size See page 49 for thread specs	Dimensions in Inches (mm)	
			G	H
			Thickness	Wrench Flats
Nickel Plated Brass				
NP-07-BR	PG 7	.11 (2.8)	.59 (15)	
NP-09-BR	PG 9	.11 (2.8)	.71 (18)	
NP-11-BR	PG 11	.12 (3)	.83 (21)	
NP-13-BR	PG 13 / 13.5	.12 (3)	.91 (23)	
NP-16-BR	PG 16	.12 (3)	1.02 (26)	
NP-21-BR	PG 21	.14 (3.5)	1.26 (32)	
NP-29-BR	PG 29	.16 (4)	1.61 (41)	
NP-36-BR	PG 36	.20 (5)	2.01 (51)	
NP-42-BR	PG 42	.20 (5)	2.36 (60)	
NP-48-BR	PG 48	.22 (5.5)	2.52 (64)	
NN-38-BR	3/8" NPT	.14 (3.5)	.75 (19)	
NN-13-BR	1/2" NPT	.12 (3)	.94 (24)	
NN-21-BR	3/4" NPT	.14 (3.5)	1.18 (30)	
NN-29-BR	1" NPT	.14 (3.5)	1.38 (35)	
NM-06-BR	M6 x 1.0	.10 (2.5)	.39 (10)	
NM-08-BR	M8 x 1.25	.10 (2.5)	.51 (13)	
NM-10-BR	M10 x 1.5	.11 (2.8)	.51 (13)	
NM-12-BR	M12 x 1.5	.11 (2.8)	.59 (15)	
NM-16-BR	M16 x 1.5	.11 (2.8)	.75 (19)	
NM-20-BR	M20 x 1.5	.12 (3)	.91 (23)	
NM-25-BR	M25 x 1.5	.14 (3.5)	1.14 (29)	
NM-32-BR	M32 x 1.5	.16 (4)	1.42 (36)	
NM-40-BR	M40 x 1.5	.18 (4.5)	1.77 (45)	
NM-50-BR	M50 x 1.5	.22 (5.5)	2.17 (55)	
NM-63-BR	M63 x 1.5	.24 (6)	2.76 (70)	

* Note: German Lloyd only applies to Nickel Plated Brass Locking Nuts.