

SPECIFICATIONS:

Rating: DC30V 1A ;
 Contact resistance: 100m Ω (Max.) ;
 Insulation resistance: DC500V 100M Ω (Min.) ;
 Withstand voltage: AC 1000V for 1 minute ;
 Operating force: 500 $\pm$ 200gf ;
 Operating Temp.: -25 $^{\circ}$ C ~ +65 $^{\circ}$ C
 Life cycle: 20,000 cycles ;
 Total Travel: 1.5 $\pm$ 0.3mm .


MATERIAL:

Frame: PBT,UL rated:94V-2 Min. ;
 Cap: POM;
 Terminal:Brass,Silver or Tin plated .





Function:

ON(1-6)-OFF

Cap Color: Black



P.C.B.LAYOUT(BottomView)



SERIES				TERMINAL DIRECTION	
GPTS203	21	1	B		
FUNCTION				BUTTON COLOR	

TS203-21-1-B

3	Added Identifying Block & TS203-21-1-B. 9-25-17
2	Added Operating Temp. 11-13-12.

CW INDUSTRIES
 Southampton, Pa. 18966
 Tel 215.355.7080/www.cwind.com

Date Drawn: 9/25/17

Rev. 3

Unit: mm

Checked By: *G. GULD*

Title:
 PUSH BUTTON SWITCH

CW P/N:
 GPTS203211B