

[»Back to Board Level Products](#)

7021B-MTG

TO-220, TO-220-single gauge (0.020")



ENTER QTY:

VIEW PRICE

Need assistance?

Call us: 1-855-32-AAVID
Email: estore@aavid.com

[» Help Page](#)

Check Distributor Stock

Enter a part number for pricing and availability.

- > [Request a Sample](#)
- > [Request a Quote](#)
- > [Ask an Engineer](#)

The Fine Print

[Product Return Policy](#)
[Terms & Conditions](#)
[Privacy Policy](#)

Channel style heat sink with folded back fins and mounting tabs

This non-electronic component is functionally unaffected by the normal soldering or reflow processes used for semiconductor circuits. The heat resistance time or heat resistance temperature is not applicable for the component.

Height: 42.16


Mount Orientation: Vertical

Finish: Black Anodize


RoHS: compliant


[Download PCN](#)

Thermal Resistance: 6.80



X Dim: 20.77 (0.820) | Y Dim: 3.81 (0.150) | Z Dim: 2.95 (0.116)





Solderable Mounting Tabs

Customer Assistance

- [Contact Us](#)
- [Find a Distributor](#)
- [Find a Sales Rep](#)
- [Request a Quote](#)
- [Get Design Assistance](#)
- [Terms and Conditions](#)
- [Returns](#)

Popular Products

- [Fans Heat Sinks](#)
- [Extrusions](#)
- [Board Level](#)
- [Liquid Cooling](#)
- [Heat Pipe Technology](#)
- [Heat Sink Accessories](#)
- [Interface Materials](#)

Our Company

- [News and Events](#)
- [Management Team](#)
- [Worldwide Locations](#)
- [Disclaimer](#)
- [Customer Survey](#)
- [Privacy Policy](#)
- [Careers](#)

Connect with Aavid

Like / Follow / Connect



© Copyright 2017 Aavid Thermalloy, LLC.

USA: 1.855.32.AAVID **Europe:** 39.051.764002 **Asia:** 86.21.6115.2000 x 8122