



**Angle type (Pitch: 2.54 mm) [Part number: OZ-001] (10pcs/pack)**

- This is used for putting PC boards at right angle.
- Pitch: 2.54 mm, 20 pins connected
- Please cut it to the desired number of poles by using a mold cutting nipper (Part number: MOC-3)
- Material Pin: Brass, Finish: Gold plating over nickel base  
Resin: PBT red (UL94V-0)
- Operating temperature range:  $-40$  to  $+125^{\circ}\text{C}$
- Printed board fitting hole diameter:  $\phi 0.8$
- Adaptive socket: PM-1



20P connected

**■ Part number: OZ-001**