

Detailed Specifications

|                             |                               |
|-----------------------------|-------------------------------|
| Frame Width:                | 80[mm]                        |
| Frame Height:               | 80[mm]                        |
| Frame Depth:                | 25[mm]                        |
| Max. Air Flow:              | 41.3[CFM]                     |
| Max. Air Flow:              | 1.17[m3 per min]              |
| Max. Static Pressure:       | 0.15[In H2O]                  |
| Max. Static Pressure:       | 37.5[Pa]                      |
| Fan Speed:                  | 3100[RPM]                     |
| Noise:                      | 30[dB]                        |
| Life Expectancy:            | 60 degree C 40,000 Hours[L10] |
| Bearing Type:               | Ball Bearing                  |
| Nominal Voltage:            | 12[V]                         |
| Operating Voltage - Lower:  | 6[V]                          |
| Operating Voltage - Upper:  | 13.8[V]                       |
| Current:                    | 0.14[A]                       |
| Input Power:                | 1.7[W]                        |
| Mass:                       | 80[g]                         |
| Tach / Locked Rotor Output: | No                            |
| Status:                     | Active                        |