

Product Line

DeepTronica >

Single Pair Ethernet >

ZConnect >

Ceres >

X-Lok >

Accessory

Middle Size

Mini Size

Large Size

Standard Size

M Series >

FLOS & FLOS+ >

Power >

RBL >

HS-Lok >

NMEA 2000 >

Heavy Duty Shielded >

RJ >

USB >

SSL >

HDMI >

DVI >

Fiber Optic >

RF >

Cable Joiner >

Cable Gland >

Pressure Relief Vent >

LED Light Guide >

D-Sub >



BB-03BFMA-QL8LPP

Operating Temperature: -40°C ~ +105°C

Transmission Speed: N/A

Shielded: Plastic, Non-shielded

Jacket Material: N/A

Certificate: UL1977


You must login first for view the price

Quantity - 1 +

 Check Stock

 Add to Cart

 Inquiry



Can't find? [Customize your part](#)

Mating Pair & Accessories

Connector Type ▼ Search



X-Lok, Accessory...
AB-BB-030303-...
-20°C ~ +85°C

- 0 +

☐



X-Lok, Standard...
AB-BB03FL-BBHL...
-20°C ~ +80°C

- 0 +

☐



X-Lok, Standard...
AB-BB03FL-BBHL...
-20°C ~ +80°C

- 0 +

☐



X-Lok, Standard...
AB-BB03FL-BBHL...
-20°C ~ +80°C

- 0 +

☐



X-Lok, Standard...
AB-BB03FL-BBHL...
-20°C ~ +80°C

- 0 +

☐



X-Lok, Standard...
AB-BB03FL-BBHL...
-20°C ~ +80°C

- 0 +

☐

Add to Cart Inquiry

Specifications		Download / CAD	
Nominal Current		Connector Type	
10A		Field Installable	
Shielded		No. of Contacts	
Plastic, Non-shielded		03	
Connector Gender		Backshell	
Female		Straight	
Mating Style		IP Rating	
Push Lock		IP68	
Assembly Style			
Crimp			
 More Options			

People Also Bought



BB-03BFMA-QL8LPP



CB-04PMFM-LL7A02



M12A12FL-12AMR-...



1CC-03BFMM-LL6A02



CB-04RFFS-RC8DA0