





DATE	REV.	ECN	APP'D BY
2-17-15	D3	10260	ADB
2-9-16	D4	10531	TRM



JACK PIN NUMBERS

SEE DETAIL
JACK PIN NUMBERS



Ø.125-.128 (2)
[3.18-3.25]
⊕ Ø.006 [0.15]

.225
[5.72]

.085
[2.16]


.080 TYP
[2.03]

.040 TYP
[1.02]

SEE DETAIL
PCB PIN NUMBERS

Ø.035 [0.89](8)
⊕ Ø.006 [0.15]

PCB PIN NUMBERS



COMPONENT SIDE

NOTES:

- CONNECTOR MATERIALS:
HOUSING: THERMOPLASTIC UL94 V-0
CONTACTS: COPPER ALLOY
CONTACT PLATING: SELECTIVE PLATING IN CONTACT AREA
SEE CHART FOR DETAILS.
- PRODUCT DESIGNED FOR CATEGORY 6 APPLICATIONS
- DIMENSIONS AND TOLERANCES COMPLY WITH TIA-1096 STANDARD.
- REFERENCE PRODUCT SPECIFICATION PR026-01

PCB RECOMMENDED HOLE LAYOUT
SEEN FROM COMPONENT SIDE


ALL CENTERLINE DIMENSIONS ARE BASIC

50 MICRO-INCHES [1.27um] Au OR
5 MICRO-INCHES [0.13um] Au OVER
30 MICRO-INCHES [0.76um] PdNi

CONTACT PLATING
IN MATING AREA

SS-60000-007


PART NUMBER



RoHS



THIRD ANGLE PROJECTION



11118 Susquehanna Trail South
Glen Rock, PA 17327-9199
(717) 235-7512

<http://www.stewartconnector.com>

CATEGORY 6 UNSHIELDED VERTICAL JACK

DO NOT SCALE DRAWING

DRAWING IS SUBJECT TO
CHANGE WITHOUT NOTICE

DIMENSIONS: INCHES [METRIC]

UNLESS OTHERWISE SPECIFIED
TOLERANCES ARE ±.005 [0.13]
ANGLES ARE ±1°

SHEET NO.

1 OF 1

THIS DRAWING AND THE SUBJECT MATTER SHOWN THEREON
ARE CONFIDENTIAL AND THE PROPRIETARY PROPERTY OF
STEWART CONNECTOR AND SHALL NOT BE REPRODUCED,
COPIED, OR USED IN ANY MANNER WITHOUT PRIOR WRITTEN
CONSENT OF STEWART CONNECTOR. ONE OR MORE U.S. PATENTS
MAY APPLY TO THIS PRODUCT. FOR DETAILS, PLEASE
VISIT: [HTTP://BELFUSE.COM/STEWART/STEWART_PATENTS/](http://BELFUSE.COM/STEWART/STEWART_PATENTS/)

DRN BY:

JRC

DATE

6-17-02

APPD BY:

DHG

DATE

6-17-02

DWG. NO.

CT600007

REV.

D4