


Part Number : [2079932001](#)

Product Description : SlimSAS Cable Assembly, PCIe 4.0, Right-Angle Plug-to-Right-Angle Plug, 8x (74 Circuits), 32 AWG, 0.30m Length

Series Number : 207993

Status : Active

Product Category : Power and Signal Cable Assemblies



Documents and Resources

Drawings

[2079932001_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	207993
Description	SlimSAS Cable Assembly, PCIe 4.0, Right-Angle Plug-to-Right-Angle Plug, 8x (74 Circuits), 32 AWG, 0.30m Length
Assembly Configuration	Dual Ended Connectors
Connector to Connector	SlimSAS-to-SlimSAS
Product Name	SlimSAS
UPC	191130023073

Electrical

Current - Maximum per Contact	0.5A
Impedance	85Ω
Voltage - Maximum	30V AC

Physical

Cable Length	0.30m
Circuits (Loaded)	74
Circuits (maximum)	74
Color - Resin	Black
Gender	Plug/Plug
Lock to Mating Part	Yes
Material - Resin	Polycarbonate
Net Weight	24.300/g
Packaging Type	Bag
Single Ended	No
Wire/Cable Type	Ribbon Cable
Wire Size (AWG)	32

This document was generated on Sep 02, 2026