




Specifications:

Contact rating:	max.: 400mA, 32V AC; 100mA, 50V DC; 125mA, 125V AC
Contact resistance:	50mOhm max.
Insulation resistance:	1GOhm min. at 500V DC
Dielectric strength:	1 000V AC
Operating temperature:	-30°C to +85°C
Mechanical life:	1 000 000 cycles
Electrical life:	500 000 cycles
Operating force:	3N +/-1N
Soldering conditions:	300°C max., 3sec.
Switching function:	off - mom
Travel:	1.5mm
Panel thickness:	0.8mm min.; 1.8mm max.
Water proofing:	IP67
Material:	Case: DAP UL94V-0 Bushing / cap: polyamide 6/6 Terminal / contact: gold over silver plated
IP rating:	IP 67 (mounted)

X=CAP COLOR	
W	white
K	black
R	red
O	orange
Y	yellow
G	green
B	blue



Tolerances: 0.00: ±0.25mm 0.0: ±0.40mm			Date	Name	DPW 1 CG S x-FO	
			07/09	dr		
Rename	11/13	dr	knitter-switch			Page 1/1
IP rating	07/11	dr				
Modifications	Date	Name				

30 18 86

Page

1/1