





HOME



会社概要

環境に対する
取り組みカタログ・サンプル
STEPファイル請求

問い合わせ

Contribute to manufacturing by delivery time, quality and service.

Employment Information

Sitemap

E-Mail: marketing@satoparts.co.jp

Part number search

Search

Search by category

Search

[Narrow search]

Applications and shapes

Shape type

- ☐ fuse
- ☐ Fuse holder horizontal type
- ☐ Fuse holder, relay type
- ☐ Fuse holder / tube type
- ☐ Fuse tube

By fuse size

- ☐ Ø5.2 × 20mm
- ☐ Ø6.35 × 30mm
- ☐ Ø6.35 × 31.8mm
- ☐ Ø6.4 × 30mm
- ☐ Ø10.31 × 38.1mm
- ☐ Ø15 × 50mm

By acquisition standard

- ☐ CSA ☐ C-UL
- ☐ PSE ☐ PSE-JET
- ☐ UL ☐ VDE

Search for

Supplementary information (PDF)

- ▶ Precautions for fuse holder
- ▶ Precautions for fuse tube
- ▶ General notes

スクリーレス端子台
Screwless Terminalネジ式端子台
Screw Terminalヒューズホルダー、
ヒューズ管[home](#) > [List of fuse holders and fuse tubes](#) > F-7135

F-7135

Notification of partial product change

- PDF** [2008/06/12 Deleted ribs and added chamfers for main body and fuse clip assembly part.](#)
- PDF** [2004/01/05 Changed fuse clip material.](#)



made in Japan

Horizontal type

[Information on RoHS Directive](#)

specification

Rating	250V-20A
Insulation resistance	DC500V, 100MΩ or more
Withstand voltage	AC1500V (1 minute)
Number of poles (P)	1
Insulating material	Phenol (UL94V-0)
Terminal screw	M4 x 8 (Sems screw): Tightening torque 1.2 Nm
Mounting screw tightening torque	0.8N ・ m: M4 screw
Terminal fitting	Screw terminal (M4)
Body color	B (black)

[Product Summary](#) / [specification](#) / [Dimensions](#) / [Ordering model number](#) / [Applicable fuse tube](#) / [download](#)

(Request a STEP file or sample of the product you are currently





HOME



ツマミ
Knob



コンセント、コネクタ
Connector



ターミナル、チップジャック
Terminal, Tip Jack



クリップ、ソケット、プラグ
Clip, Socket, Plug



ブッシング、ラグ板
Bushing, Lug



アクセサリ
Accessory

販売中止品



製品一部変更





会社概要




環境に対する
取り組み



カタログ・サンプル
STEPファイル請求



問い合わせ



Technical drawing of the product showing top, side, and cross-sectional views. Dimensions are provided in millimeters (mm). The top view shows a rectangular component with a central circular feature and four corner features. The side view shows a U-shaped profile with a total height of 30 mm and a base width of 15.5 mm. The cross-sectional view shows a U-shaped profile with a total height of 21.5 mm and a base width of 15.5 mm. The central circular feature has a diameter of 9.2 mm. The corner features have a diameter of 4.6 mm. The component is made of M4 x 8 sems (semiconductor).

Unit: mm

Ordering model number

Ordering model number F-7135
Ordering example F-7135

Applicable fuse tube

Ø10.31 × 38.1mm



[F-7165](#)

DXF / environmentally hazardous substance report (chemSHERPA) Download

* Please read the [DXF file terms of use](#) when downloading the [DXF file](#) .
* For the report on environmentally hazardous substances , see [Environmental Activities](#) .
* For the tool for viewing chemSHERPA data, see the [PDF download procedure manual](#) .
In addition, with regard to the survey list, [PDF click here](#) please refer to.

Model number	DXF file	Environmental Impact Substance Report (chemSHERPA)
F-7135	download	download

HOME | Company Profile | Terms of use | privacy policy | site map

Product Summary / specification / Dimensions / Ordering model number / Applicable fuse tube / download

(Request a STEP file or sample of the product you are currently

www.satoparts.co.jp/JPN/item/F/F-7135/

Downloaded from [Arrow.com](#)

2/3

