



ML-30-AP



ML-30-BP



Enlarge : Click picture, drawing.

| [Back](#) | [List](#) | [Next](#) |

To be Followed by part number.

Specification



Rating	250V-6A
With standing V	AC2000V(1minute)
Insulation Ω	DC500V,100M Ω Min
Safety approvals	UL,CSA,TÜV
Number of poles	1 up to 20
Insulation materials	Phenol(UL94V-0)
Pitch	9.45mm
Screw	M3X6
Terminal style	PCB
Body color	Black
Important notice	Except 20 Poles remaining scratch marks at the end due to cutting by pole

How To Order

ML - 30 -  		
Series	Style	Number of poles
ML - 30	A P : Vertical	1 up to 20
	B P : Horizontal	

ML-30-AP

ML-30-BP



UP DATE: 6/30/2006

[Back](#)

[Home](#)

- The contents of these document are subject to change without previous notice for improvements in product performance.
- When using the products, please confirm with the soecifications which will provided to you upon request.Individual specifications prior to the catalog specification.
- The appearance of product's color may different from original upon your monitor or operating system.
- The latest information to receive please cosult our marketing either phone call or e-mail.

e-mail: marketing@satoparts.co.jp

[| Company profile](#) | [| Site map](#) | [| Ask](#) | [| Notice and hint](#) | [| Renewal record](#) | [| Japn Web site](#) |

Copyright (C) 2001-2006 SATO PARTS CO., LTD. All Right Reserved.