


NOTES:

1. PACKAGING ACC. TO TE SPEC.107-18032
BUNDLE EVERY 25 ASSEMBLIES WITH A RUBBER BAND
2. ELECTRICAL TEST CONTAINING "SHORT CIRCUIT TEST, CONTINUITY
AND ACCURATE CAVITY ASSIGNMENT TEST" ACC. TO
TE-SPEC.108-18857, SUBSECTION 3.1.1

- 3 WIRING SCHEDULE AS SHOWN
- 4 PROP 65 WARNING LABEL, SEE SHEET 2



WIRING SCHEDULE		
CONNECTOR	SIDE	
1	RIBBED	+
2	SMOOTH	-

3

OBSOLETE	16.0 FT	±3.84	2181148-8
	14.0 FT	±3.36	2181148-7
	12.0 FT	±2.88	2181148-6
	10.0 FT	±2.4	2181148-5
	8.0 FT	±1.92	2181148-4
	6.0 FT	±1.44	2181148-3
	4.0 FT	±.96	2181148-2
4	2.0 FT	±.48	2181148-1
	"L"	TOLERANCES [INCHES]	TE P/N

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN E.C. CLAYBAUGH 10/JUN/11	TE Connectivity	
DIMENSIONS: INCHES		CHK P. BECKER 13/JUL/11		
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME CABLE ASSEMBLY, NECTOR, HV-2, PLUG-PIGTAIL	
	0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		SIZE A2	
	MATERIAL -		CAGE CODE 00779	
FINISH -		APVD P. BECKER 01/AUG/11	DRAWING NO C-2181148	
		PRODUCT SPEC -	RESTRICTED TO -	
		APPLICATION SPEC -		
		WEIGHT -		
CUSTOMER DRAWING			SCALE NTS	SHEET 1 of 2
			REV A2	

