



Johanson Product Information for LRC0603CS1N5GV001T

Johanson Company: Johanson Technology inc.

Termination: Ni/Sn (RoHS)

Deprecated P/N: L-14C1N5SV4T

Marking: No Mark

Datasheet Date: 08-07-2022

Product Release Date: 04 January, 2006

Description: Ceramic Inductor, 0603, 1.5nH $\pm$ 0.3nH, 300mA, Ni/Sn (RoHS), No Mark, 7" Reel Paper Tape

Web Page Link:

<https://www.johansontechnology.com/ceramic-inductors>

Life Cycle Stage: Active - Production

NCNR: No

AEC Q200 Qualified: No

Thickness (Max): 0.039

Schedule B: 8504.50.0000

Thickness (Min): 0.023

Harmonization Code: 8504.50.40.00

End Band (Min): 0.008

ITAR: No

End Band (Max): 0.016

ECCN: EAR99

Standard Item: No

RoHS Compliance: Yes, RoHS 10/10

Lead Time Typical (Weeks)*:

*This can vary significantly so it is important to obtain a quotation with lead time for production planning purposes. 14

REACH: Yes

Country of Origin: TW

Length (Min): 0.057

Product Family: Inductors

Length (Max): 0.069

Product Subfamily: Ceramic Inductors

Width (Min): 0.023

Tolerance: $\pm$ 0.3nH

Width (Max): 0.039