






PART NO.	A	B	C	D	E
PCR-S20PMLA2+S	33.4	28.4	42.0	10.4	—
PCR-S28PMLA2+S	38.5	33.5	43.0	14.5	16.5
PCR-S36PMLA2+S	43.6	38.6	43.0	16.0	18.0
PCR-S50PMLA2+S	52.5	47.5	45.0	17.0	19.0

NOTE1. COVER A AND B (ITEM#1 AND 2) FOR 28, 36 AND 50 POS. CONNECTORS HAVE A PROTRUSION.

				7	EARTH METAL	COPPER ALLOY	1	Sn PLATING	—————	
				6	⊕PAN HEAD SCREW	STEEL	2	NI PLATING	M2×8	
				5	CABLE CLAMP	STEEL	2	NI PLATING	—————	
				4	HEX. NUT	STEEL	2	NI PLATING	M2.6	
△3				3	⊕PAN HEAD SCREW	STEEL	2	NI PLATING	M2.6×10	
△2				2	COVER B	ABS	1	—————	UL94V-0, GRAY	
△1				1	COVER A	ABS	1	—————	UL94V-0, GRAY	
LTR.	DATE	BY	REV.	DESCRIPT	No.	PART NAME	MATERIAL	QTY	FINISH	NOTE
DATE Jun 28 (2004)		SCALE 2/1		UNIT mm (INCH)		3RD. A. P	HONDA TSUSHIN KOGYO CO., LTD.			
APP. DATE&REV.										
DR.		DE.		CHK.		CHK.		APP.		NAME PCR-E () PMRS TYPE PLASTIC COVER FOR CABLE EXTENSION (RoHS)
T. KAWANO		T. KAWANO		T. SOGO		K. HOMMA		S.FURUSAWA		
PART NO.		PCR-S () PMLA2+S				REV.				