




# TP1010LF, Vinyl Locking Fork Terminal, 12-10 AWG, #10 Stud

By Burndy  
Catalog # [TP1010LF](#)



Vinyl Locking Fork Terminal, 12-10 AWG, #10 Stud, Fast Installation with Security

### Features

- Locking fork tongue design allows fast installation
- Screw only has to be loosened for termination
- Internal configuration of the fork prevents the terminal from coming off the screw without applying a pulling force
- Locking fork is made from a copper alloy and permits many installations while maintaining proper spring retention of forks

### Application

For Fast Installation And Security

### Specifications

|                                    |                      |
|------------------------------------|----------------------|
| Certification - UL Recognized      | No                   |
| Buy American Compliant             | Contact Manufacturer |
| Certification - cULus              | No                   |
| Certification - ETL                | No                   |
| Standards - Industry Standards Met | UL486                |
| Standards - RoHS Compliance        | CM                   |
| Status                             |                      |
| UL Listed                          | Yes                  |
| Certification - CSA Approved       | Yes                  |

### Conductor

|                 |                    |
|-----------------|--------------------|
| Conductor Size  | 12 - 10 AWG        |
| Conductor Type  | CU C Str-Size      |
| Conductor Range | #12 AWG to #10 AWG |

### Configuration

|                                      |                       |
|--------------------------------------|-----------------------|
| Physical Attribute - Number of Holes | 1                     |
| Connector Type                       | Locking Fork Terminal |

### Current

|                   |       |
|-------------------|-------|
| Voltage - Maximum | 600 V |
|-------------------|-------|

### Dimensions

|                                |          |
|--------------------------------|----------|
| Dimension - Pad Width inch     | 0.36 in  |
| Package Height                 | 0.000 in |
| Dimension - Hole Size fraction | 15/79    |

|                                   |           |
|-----------------------------------|-----------|
| Package Weight                    | 0.000 lb. |
| Package Length                    | 0.000 in  |
| Package Width                     | 0.000 in  |
| Dimension - L Length Overall mm   | 29 mm     |
| Dimension - Hole Size inch        | 0.19 in   |
| Dimension - Strip Length inch     | 11/32 in  |
| Dimension - Stud Size inch        | #10       |
| Dimension - Bolt Size fraction    | #10       |
| Dimension - B Length fraction     | 17/50 in  |
| Dimension - Z inch                | 0.31 in   |
| Dimension - B Length inch         | 0.34 in   |
| Dimension - Length Overall inch   | 1.16 in   |
| Cable Insulation Diameter Maximum | 0.260 in  |

### General

|                                  |                |
|----------------------------------|----------------|
| Product Family                   | COMPRESSION    |
| Insulation Type                  | Vinyl          |
| Trade Name                       | VINYLUG™       |
| Insulation                       | Y              |
| Feature - Barrel Style           | Shrouded       |
| Plated                           | Yes            |
| Color Code                       | Yellow         |
| Physical Attribute - Tongue Type | Locking Fork   |
| Sub Brand                        | VINYLUG        |
| Product Type                     | Terminal       |
| UPC                              | 781810713907   |
| Type                             | TP-LF, Locking |
| Material                         | Copper         |
| Plating Type                     | Tin            |
| UPC 12 Digit                     | 781810713907   |
| UPC 14 Digit GTIN                | 00781810713907 |

### Logistics

|                       |       |
|-----------------------|-------|
| Minimum Pack Quantity | 50    |
| Pallet Quantity       | 99999 |
| Carton Quantity       | 600   |

### Product Assets

[Catalog \[English\]](#)

