

[Labels](#) / [Labels by Application](#) / [Barcode Labels](#) /

3" Core Series UltraTemp 1-Mil Matte Polyimide Labels

3" Core Series UltraTemp 1-Mil Matte Polyimide Labels





Product Highlights

Label/Tape Size:

0.375 in H x 0.375 in W

Color:

White

For Use with Printer:

BBP®81 Label Printer, BRADY IP® Series Label Printer, BradyPrinter i5100, BradyPrinter i7100, BRADYPRINTER PR Plus Series Label Printer, THT 3" Core Printer

Material:

Polyimide

Material Number:

B-719

Finish:

Matte

Label Properties:

Heat Resistant Labels, Permanent Adhesive Labels

Part Number:

THT-38-719-10

ADD TO CART

1



Need a different size? Customize it!



Calculate how many labels you can print with one ribbon



Overview

Static Dissipative Polyimide (B-719) withstands wave solder environments and multiple harsh washes for printed circuit board and electronic component preprocess labeling.

- Low profile, high temperature, matte white polyimide material features a static dissipative adhesive and static dissipative release liner
- Surface resistivity values in the recommended range for Dissipative ESD packaging materials as defined by ANSI/ESD S541-2008
- UL Approved; Meets requirements of MIL-STD-202G, Method 215K
- Service temperature of -94 to 212° F (-70 to 100° C)

Specifications

Material Number	B-719
Country of Origin	US - All trade information (i.e. Country of Origin, Harmonized Schedule code, and/or Export Control Classification Number) and related assistance provided by Brady Corporation and its affiliates is provided for informational purposes only and is subject to change without notice. Any use of such information by you is without recourse to Brady Corporation or its affiliates and is at your own risk. This information is not provided as legal advice or as a substitute for obtaining specific legal advice. If you have any questions regarding your specific situation, you should consult your attorney.
California Prop 65	WARNING: Cancer - www.p65warnings.ca.gov
Catalog Page #	175
Dimensions	0.375 in H x 0.375 in W
UOM	Roll of 10000 Labels
Finish	Matte
Label/Tape Size	0.375 in H x 0.375 in W
Maximum Service Temperature °F	572 °F

Meta Description	Brady THT-38-719-10 is a High-Temperature ESD Industrial Polyimide Barcode Label that is 0.375" X 0.375" (9.530 mm X 9.530 mm). Shop online!
Meta Title	BRADY THT-38-719-10 ESD BARCODE LABEL
Minimum Service Temperature °F	-94 °F
Product Number	134307
UPC	754473924898
Quantity per Roll	10000
Quantity per Row	7
Thickness	0.0033 in
Trade Name	UltraTemp®
Unit Price	/Label
UNSPSC	55121612
Adhesive Type	Acrylic
Applications	Circuit Board ID - After Process, Circuit Board ID - Surface Mount, Circuit Board ID - Through Hole Bottom, Circuit Board ID - Through Hole Top, Circuit Board Marking
Color	White
For Use with Printer	BBP®81 Label Printer, BRADY IP® Series Label Printer, BradyPrinter i5100, BradyPrinter i7100, BRADYPRINTER PR Plus Series Label Printer, THT 3" Core Printer
Label/Media Format	Roll
Label Properties	Heat Resistant Labels, Permanent Adhesive Labels
Material	Polyimide
Material Properties	Low Profile, Static-dissipative
Patent Number(s)	5958537
Patent Valid in (Countries)	USA
Printer and Label Applications	Circuit Board
Print Technology	Thermal Transfer
Shape	Square
Suggested Ribbon Series	R4700, R6000

Solutions

[Floor Marking Guide](#)

Services

[Lockout Tagout Services](#)

Help

[Contact Us](#)

Resources

[Find a Distributor](#)

GHS Label Compliance
Lockout Tagout Compliance
Arc Flash Labeling Requirements
Cable and Wire Label Options
Product and Barcode Labeling

Arc Flash Services
Confined Space Services
Software Programming & Integration
Label Template & File Conversion
Printer Use & Training
Printer Preventative Maintenance
Toll and Custom Coating
Authentication & Tracking Services

Website Feedback
Knowledge Center
Printer Drivers & Firmware
Brady Software Updates
Safety Data Sheets
Technical Data Sheets
WEEE-RoHS Compliance
Product Certification
Printer Registration


Design Custom Safety Signs
Create Custom THT Labels
Printer Selection Tool
Label Selection Tool
Digital Catalog
Request a Catalog
Interactive Facility Map
EPA e-Manifest Update

Corporate **Other BradyContact Sites**

[About](#)
[Careers](#)
[Investors](#)
[Privacy Policy](#)
[Terms and Conditions](#)
[Terms of Use](#)
[ISO Certificates](#)
[Distributor Portal](#)
[International Sites](#)
[Safety Services & Software](#)
[Brand Protection Solutions](#)

6555 W. Good Hope Rd.
Milwaukee, WI 53223
Phone: 888-250-3082
Hours: 7am-6pm CT
Monday - Thursday;
Friday 7am-5pm CT

Brady (NYSE:BRC) is a manufacturer of complete solutions that identify and protect people, products and places. Brady's products help customers increase safety, security, productivity and performance and include high-performance labels, signs, safety devices, printing systems and software.



2019 © Brady Worldwide, Inc.