





THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTIONS IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	CHANGED BY
E	ECN 8473-UPD DWG TO MATCH NEW DESIGN, ADD MATERIAL & NOTE 3 INFO	09/02/2016	DCUI
F	ECN 8516-UPD NOTES 2&3, UPD CABLE DESCRIPTION, ADD A VIEW	10/20/2016	DCUI
G	ECN 12067-REVISED NOTES AND FORMAT, ADDED NOTE 2, REMOVED -SM	09/04/2022	GUTTAIDAURO



PART NUMBER	LENGTH	
	FEET	METERS
WPUSBMB5X-03M	.98	[.3]
WPUSBMB5X-05M	1.64	[.5]
WPUSBMB5X-1M	3.28	[1.0]
WPUSBMB5X-2M	6.56	[2.0]

- NOTES:**
- CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY
 - SUGGESTED MAX. TORQUE VALUE FOR HEX NUT IS 0.4N-m (3.5 lbf-in)
 - INGRESS PROTECTION RATING IS IP67 (J1 ONLY, MATED)
 - CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031

REGULATORY COMPLIANCE:
EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm].

OVERALL CABLE LENGTH TOLERANCE:
≤12 [305] = +1 [25] / -0
>12 [305] ≤60 [1524] = +2 [51] / -0
>60 [1524] ≤120 [3048] = +4 [102] / -0
>120 [3048] ≤300 [7620] = +6 [152] / -0
>300 [7620] = +5% / -0

ALL OTHER DIMENSIONAL TOLERANCES:
.XX = ±.02 [5] FRACTIONS
.XXX = ±.005 [13] ANGLES ±1°

THIRD-ANGLE PROJECTION

APPROVALS

DRAWN BY: D.CASTRO 04/17/2009

CHECKED BY: D.FRISIELLO 04/20/2009

APPROVED BY: S.S.MITH 04/20/2009

CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY

COLOR VARIATIONS MAY OCCUR

DATE

04/17/2009

04/20/2009

04/20/2009

L-com
an INFINITI® brand

50 High Street, West Mill,
North Andover, MA 01845 USA.
Phone: 1.800.341.5266
1.978.682.6936

CATEGORY

USB

PRODUCT DESCRIPTION

CA WTR PR USBMB5-F/MB5-M

SIZE

B

CAGE CODE

43321

ITEM NO.

WPUSBMB5X

SCALE: NONE

CAD FILE: WPUSBMB5X.LDDRW

SHEET 1 OF 1