





HTB CONNECTOR

Assembly layout

Top entry type





Side entry type





Receptacle

Top entry type



Side entry type



Circuits	Model No.		Q'ty / reel
	Top entry type (Between PC boards 16mm)	Side entry type	
30	—	30RS-HTBK-06-TF	250
40	40R16-HTBK-06-TF	—	300



Material and Finish

Contact: Copper alloy, nickel-undercoated, selective gold-plated
Housing: Glass-filled PA 9T, UL94V-0
Reinforcement: Copper alloy, nickel-undercoated, selective gold-plated

RoHS compliance

Note: This products listed above are supplied on embossed-tape.

Shrouded header



Circuits	Model No.	Dimensions (mm)				Q'ty / reel
		A	B	C	D	
30	30H-HTBK-06-TF	8.89	11.2	13.9	16.0	250
40	40H-HTBK-06-TF	12.065	14.4	17.1	19.2	250

Material and Finish

Contact: Copper alloy, nickel-undercoated, selective gold-plated
Housing: Glass-filled PA 9T, UL94V-0
Reinforcement: Copper alloy, nickel-undercoated, selective gold-plated

RoHS compliance

Note: This products listed above are supplied on embossed-tape.