



Color: ☐ multi-colored

Physical data		
Pin spacing		4/8 mm
Blade width		4 mm
Blade length		40 mm
Grip length		100 mm

Mechanical data		
Suitable		for 2060 Series
Tip type		Operating
Continuous blade		No
Blade type		Straight
Roll-away protection		Yes
Hanging eyelet		Yes
Grip marking		Yes
Design		metal; partially insulated

Material data		
Color		multi-colored
Material 1		Polypropylen (PP)
Material 2		Thermoplastische Elastomere (TPE)
Blade surface		Burnished
Weight		24.5 g



Commercial data	
Product Group	14 (Tools)
PU (SPU)	5 pcs
Packaging type	Box
Country of origin	DE
GTIN	4050821827726
Customs tariff number	82055980000

Product Classification	
UNSPSC	27111601
eCl@ss 10.0	27-14-11-92
eCl@ss 9.0	27-14-11-92
ETIM 9.0	EC002848
ETIM 10.0	EC002848
ECCN	NO US CLASSIFICATION

Environmental Product Compliance	
RoHS Compliance Status	Compliant, No Exemption

Downloads

Environmental Product Compliance

Compliance Search

Environmental Product Compliance 206-860

↓

Installation Notes

Conductor termination



Inserting/removing fine-stranded conductors by lightly pressing on a push-button.