



ALTERNATE UNITS FOR REFERENCE ONLY

PART NUMBER	PART NUMBER	THREAD	"SW-2"	"T"
COLOUR: GREY RAL 7035 SPECIAL ORDER NAFTA	COLOUR: BLACK RAL 9005 SPECIAL ORDER EU	SIZE	±0.5[.020]	REF
CGLN-M12	CGLN-M12-BK	M12	17[.669]	5[.197]
CGLN-M16	CGLN-M16-BK	M16	22[.866]	
CGLN-M20	CGLN-M20-BK	M20	27[1.063]	6[.236]
CGLN-M25	CGLN-M25-BK	M25	32[1.260]	
CGLN-M32	CGLN-M32-BK	M32	41[1.614]	7[.276]
CGLN-M40	CGLN-M40-BK	M40	50[1.969]	
CGLN-PG7	CGLN-PG7-BK	PG7	19[.748]	
CGLN-PG9	CGLN-PG9-BK	PG9	22[.866]	5[.197]
CGLN-PG11	CGLN-PG11-BK	PG11	24[.945]	
CGLN-PG13.5	CGLN-PG13.5-BK	PG13.5	27[1.063]	6[.236]
CGLN-PG16	CGLN-PG16-BK	PG16	30[1.181]	
CGLN-PG21	CGLN-PG21-BK	PG21	36[1.417]	7[.276]
CGLN-PG29	CGLN-PG29-BK	PG29	46[1.811]	
CGLN-PG36	CGLN-PG36-BK	PG36	60[2.362]	8[.315]
*CGLN-NPT-3/8	CGLN-NPT-3/8-BK	NPT-3/8	22[.866]	5[.197]
*CGLN-NPT-1/2	CGLN-NPT-1/2-BK	NPT-1/2	27[1.063]	6[.236]
*CGLN-NPT-3/4	CGLN-NPT-3/4-BK	NPT-3/4	36[1.417]	
*CGLN-NPT-1	CGLN-NPT-1-BK	NPT-1	42[1.654]	7[.276]
*SPECIAL ORDER EU REGION				



NOTES:
TEMPERATURE RANGE -20 °C TO +100 °C

REV.	MODIFICATION.	DATE	DRN
01	Production release	19/01/10	MT
02	CO2010958	15/07/10	MT

INFORMATION CONTAINED IN THIS DOCUMENT IS CONFIDENTIAL TO RICHCO INTERNATIONAL Co. Ltd. AND MAY NOT BE DISCLOSED OR REPRODUCED IN WHOLE OR PART WITHOUT THEIR WRITTEN CONSENT.		ALL DIMENSIONS IN mm[inch] GENERAL TOLERANCES UNLESS OTHERWISE STATED 1 DECIMAL PLACE ± 2 DECIMAL PLACES ± ANGULAR ±1°	THIRD ANGLE
RICHCO, INC. WWW.RICHCO-INC.COM			
MATERIAL: NYLON 6 GF30 (RMS-044)		COLOUR: SEE TABLE	
DESCRIPTION: CABLE GLAND LOCK NUTS		PART No: CGLN-XX	
DRG No: 09-112	NPR No: EU09-0034	SHEET SIZE A4	
DRN MT	DATE 09/04/09	CHKD TC	DATE 08/10/09
		SCALE NTS	SHEET No. 1 OF 1
FORM No. 0143/00			