

[Back](#)
**Selected Cable: 17273A**

| End View | Plug                                                                              | Cord                                                                              | Connector                                                                         | End View                                                                           |
|----------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|------------------------------------------------------------------------------------|
|          |  |  |  |  |
| 5-15P    | AEC-30                                                                            | SJT                                                                               | 250A                                                                              | C13                                                                                |

|                                   |                                                             |
|-----------------------------------|-------------------------------------------------------------|
| <b>Part Number</b>                | 17273A                                                      |
| <b>Category</b>                   | 3 conductor plastic detachable special use cords            |
| <b>Jacket Color</b>               | black                                                       |
| <b>Length Feet</b>                | 10': 2' legs                                                |
| <b>Temperature Rating</b>         | 60 C°                                                       |
| <b>Packaging Units Per Carton</b> | B-50                                                        |
| <b>Color Coding</b>               | North America                                               |
| <b>AWG Stranding</b>              | 18 (41x34)                                                  |
| <b>Nominal OD Inch</b>            | 0.315                                                       |
| <b>Nominal OD millimeter</b>      | 8                                                           |
| <b>Rating</b>                     | 1250 Watts 10A-125V                                         |
| <b>Notes</b>                      | See 17272A for 6' version. See 17275A for 16 gauge version. |

**Cord View****Approvals**



Qty:

Back

Volex Power Cord Products Division, 5350 Lakeview Parkway S. Drive #D Indianapolis, IN 46268  
800-246-CORD. [info@volexpowercords.com](mailto:info@volexpowercords.com)

Proposition 65 warning for California residents: This product contains chemicals, including lead, known to the State of California to cause (cancer, and) birth defects or other reproductive harm. Wash hands after handling.

