

Part number

# CK 03 IA



Angled Bulkhead mounting housing, CK series,  
with 1 lever without cable entry, size 21.21,  
white colour

| Product description                    |                                  | Material properties          |                                      |
|----------------------------------------|----------------------------------|------------------------------|--------------------------------------|
| Product type                           | Angled bulkhead mounting housing | Other materials              | Lever: Polyamide (PA)<br>Gasket: TPE |
| Series                                 | CK                               | Colour                       | RAL 7035 grey                        |
| Closing type                           | With 1 lever                     | RoHs conformity              | Compliant                            |
| Size                                   | Size "21.21"                     | China RoHs - EFUP            | E                                    |
| Cable entry                            | Without cable entry              | REACH SVHC substances        | No                                   |
| Specification                          | White colour                     | Approvals / Standards        |                                      |
| Technical data                         |                                  | UL                           | ECBT2                                |
| IP degree of protection                | 4679                             | cUL                          | ECBT8                                |
| Further technical details              |                                  | General ordering information |                                      |
| Mating cycles                          | ≥ 500                            | EAN13 code                   | 8015747026277                        |
| Weight                                 | 12,85 g                          | eCl@ss 8.1                   | 27440202                             |
| Operating temperature range (min, max) | -40°C...+125°C                   | ETIM 7.0                     | EC000437                             |
|                                        |                                  | Packaging Information        |                                      |
|                                        |                                  | Packaging length             | 360,00 mm                            |
|                                        |                                  | Packaging height             | 165,00 mm                            |
|                                        |                                  | Packaging width              | 315,00 mm                            |
|                                        |                                  | Packaging weight             | 1,70 kg                              |
|                                        |                                  | Packaging volume             | 18,71 dm <sup>3</sup>                |
|                                        |                                  | Packaging description        | Carton box                           |
|                                        |                                  | Packaging quantity           | 100 Pcs                              |
|                                        |                                  | Packaging EAN code           | 8015747026284                        |
|                                        |                                  | Sub-packaging weight         | 0,17 kg                              |
|                                        |                                  | Sub-packaging description    | Plastic bag                          |
|                                        |                                  | Sub-packaging quantity       | 10 Pcs                               |
|                                        |                                  | Sub-packaging EAN barcode    | 8015747026291                        |


Part number

# CK 03 IA




Catalogue drawings


**CK IA(N)**



**CK IAP(N)S - MK IAP (N)**



Catalogue drawings



## Notes

Dimensions shown in mm are not binding and may be changed without notice.