

Product Line

- DeepTronica >
- Single Pair Ethernet >
- ZConnect >
- Ceres >
- X-Lok >
- M Series >
- FLOS & FLOS+ >
- Power >
- RBL >
- HS-Lok >
- NMEA 2000 >
- Heavy Duty Shielded >
- RJ >

- Middle Size
- Large Size
- ODVA
- Accessory

- USB >
- SSL >
- HDMI >
- DVI >
- Fiber Optic >
- RF >
- Cable Joiner >
- Cable Gland >
- Pressure Relief Vent >
- LED Light Guide >
- D-Sub >



CAP-WACMTMA1

Operating Temperature: -40°C ~ +105°C
Transmission Speed: N/A
Shielded: Plastic, Non-shielded
Jacket Material: N/A
Certificate: N/A

You must login first for view the price

Quantity - 1 +

 Check Stock

 Add to Cart

 Inquiry



Can't find? [Customize your part](#)

Mating Pair & Accessories

Connector Type ▼ Search



RJ, Middle Size...
RCP-5SPFFB-...
-20°C ~ +80°C

- 0 +

☐



RJ, Middle Size...
RCP-5SPFFB-...
-20°C ~ +80°C

- 0 +

☐



RJ, Middle Size...
RCP-5SPFFB-...
-20°C ~ +80°C

- 0 +

☐



RJ, Middle Size...
RCP-5SPFFB-...
-20°C ~ +80°C

- 0 +

☐



RJ, Middle Size...
RCP-5SPFFB-...
-20°C ~ +80°C

- 0 +

☐



RJ, Middle Size...
RCP-5SPFFB-...
-20°C ~ +80°C

- 0 +

☐

Add to Cart Inquiry

Specifications	Download / CAD
Nominal Current N/A	Connector Type Waterproof Cap
Shielded Plastic, Non-shielded	No. of Contacts N/A
Connector Gender Male	Backshell N/A
Mating Style 3 Points Lock	IP Rating N/A
Assembly Style N/A	
➕ More Options	

People Also Bought

- 

CAP-WACMTMA1
- 

AB-BB03HL-BBBL-...
- 

CD-12PMMP-LC7001
- 

DC-04BFMB-QL8LPP
- 

M8S03FR-SFR-...