


Inductor

TCK-102


Order Code	TCK-102
Inductance	3.3 µH ±20% (at 100 kHz / 250 mV)
Impedance (DCR)	18 mΩ max.
Rated Current	10 A max.
Operating Temperature	-40°C to +125°C
RoHS Exemptions	No Exemptions
Overview Link	www.tracopower.com/overview/tck-102



Impedance Curve



Outline Dimensions



All specifications valid at +25°C, unless otherwise stated.