

Product Line

- [DeepTronica](#) >
- [Single Pair Ethernet](#) >
- [ZConnect](#) >
- [Ceres](#) >
- [X-Lok](#) >
- [M Series](#) >
- [Accessory](#)
- [M5](#)
- [Guided M8](#)
- [M8](#)
- [M10.5](#)
- [M12 \(A\)](#)
- [M12 \(B\)](#)
- [M12 \(D\)](#)
- [M12 \(I\)](#)
- [M12 \(K\)](#)
- [M12 \(L\)](#)
- [M12 \(S\)](#)
- [M12 \(T\)](#)
- [M12 \(X\)](#)
- [M23](#)
- [FLOS & FLOS+](#) >
- [Power](#) >
- [RBL](#) >
- [HS-Lok](#) >
- [NMEA 2000](#) >
- [Heavy Duty Shielded](#) >
- [RJ](#) >
- [USB](#) >
- [SSL](#) >
- [HDMI](#) >
- [DVI](#) >
- [Fiber Optic](#) >
- [RF](#) >
- [Cable Joiner](#) >
- [Cable Gland](#) >
- [Pressure Relief Vent](#) >
- [LED Light Guide](#) >
- [D-Sub](#) >
- [ALTW Emporium](#) >



SM12A-05PMMS-SF8001

Operating Temperature: -40°C ~ +105°C
Transmission Speed: N/A
Shielded: Stainless, Non-shielded
Jacket Material: N/A
Certificate: UL1977, UL2238, UL1863

You must login first for view the price

Quantity Check Stock

Add to Cart Inquiry

Can't find? [Customize your part](#)

Mating Pair & Accessories

Connector Type Search

M Series....
CAP-WBDM0PC1
-20°C ~ +80°C

M Series....
CAP-WBDMSMA2
-40°C ~ +105°C

M Series....
CAP-WBDMSPB2
-40°C ~ +105°C

M Series....
DB12-5A4CAB-...
-20°C ~ +85°C

M Series....
DB12-5A4CAB-...
-20°C ~ +85°C

M Series....
DB12-5A4CAB-...
-20°C ~ +85°C

Add to Cart Inquiry

Specifications	Download / CAD
Nominal Current 4A	Connector Type Receptacle
Shielded Stainless, Non-shielded	No. of Contacts 05
Connector Gender Male	Backshell Hexagonal
Mating Style Screw Thread	IP Rating IP68
Assembly Style Solder	
More Options	

People Also Bought

- 

SM12A-05PMMS-SF8001
- 

AB0-06BFMM-LL7A10
- 

RDP5SM-SPG06M-SF8001
- 

DU-21AFFM-LL7A03
- 

BP-048MMM-SL7A04