

[Products](#)[Customize Your Parts](#)[Industries Solutions](#)[Search](#)[News & Events](#)[First Time?](#)

[Home](#) / [Products](#) / [Ceres](#) / [Standard Size](#)

## Product Line

Single Pair Ethernet >

ZConnect >

Ceres >

- Accessory
- Large Size
- Macro Size
- Middle Size
- Mini Size
- Others (GBD)
- Others (MAB)
- Others (PLD)
- Standard Size

X-Lok >

M Series >

FL0S & FL0S+ >

Power >

RBL >

HS-Lok >

NMEA 8888 >

### ABOUT AMPHENOL LTW

Heavy Duty Shielded >

RJ >

USB >

SSL >

HDMI >

DVI >

Fiber Optic >

RF >

Cable Joiner >

Cable Gland >

Pressure Relief Vent >

LED Light Guide >

D-Sub >



## BU-10PMMM-LL7A01

Operating Temperature: -20°C ~ +80°C

Transmission Speed: N/A

Shielded: Plastic, Non-shielded

Jacket Material: PVC

Certificate: N/A

You must login first for view the price

Quantity 

- 1 +

Add to Cart

Inquiry

Can't find? [Customize your part](#)

## Mating Pair & Accessories

Connector Type

Search

### ABOUT AMPHENOL LTW

Heavy Duty Shielded >

RJ >

USB >

SSL >

HDMI >

DVI >

Fiber Optic >

RF >

Cable Joiner >

Cable Gland >

Pressure Relief Vent >

LED Light Guide >

D-Sub >

### SUPPORT

### PARTNERS

### DOWNLOAD CENTER

### FEEDBACK

Add to Cart

Inquiry

| Specifications                           | Download / CAD                                 |
|------------------------------------------|------------------------------------------------|
| Nominal Current<br><b>2A</b>             | Connector Type<br><b>Receptacle With Cable</b> |
| Shielded<br><b>Plastic, Non-shielded</b> | No. of Contacts<br><b>10</b>                   |
| Connector Gender<br><b>Male</b>          | Backshell<br><b>Straight</b>                   |
| Mating Style<br><b>2 Points Lock</b>     | IP Rating<br><b>IPX7</b>                       |
| Assembly Style<br><b>N/A</b>             |                                                |
| <div> More Options</div>                 |                                                |

## People Also Bought

