

Product Line

- [DeepTronica](#) >
- [Single Pair Ethernet](#) >
- [ZConnect](#) >
- [Ceres](#) >
- [X-Lok](#) >
- [M Series](#) >
- [Accessory](#)**
- [M5](#)
- [Guided M8](#)
- [M8](#)
- [M10.5](#)
- [M12 \(A\)](#)
- [M12 \(B\)](#)
- [M12 \(D\)](#)
- [M12 \(I\)](#)
- [M12 \(K\)](#)
- [M12 \(L\)](#)
- [M12 \(S\)](#)
- [M12 \(T\)](#)
- [M12 \(X\)](#)
- [M23](#)**
- [FLOS & FLOS+](#) >
- [Power](#) >
- [RBL](#) >
- [HS-Lok](#) >
- [NMEA 2000](#) >
- [Heavy Duty Shielded](#) >
- [RJ](#) >
- [USB](#) >
- [SSL](#) >
- [HDMI](#) >
- [DVI](#) >
- [Fiber Optic](#) >
- [RF](#) >
- [Cable Joiner](#) >
- [Cable Gland](#) >
- [Pressure Relief Vent](#) >
- [LED Light Guide](#) >
- [D-Sub](#) >



CAP-WBDM SMA2

Operating Temperature: -40°C ~ +105°C
Transmission Speed: N/A
Shielded: Metal, Non-shielded
Jacket Material: N/A
Certificate: N/A

You must login first for view the price

Quantity - 1 + Check Stock

Add to Cart Inquiry 

Can't find? [Customize your part](#)

Mating Pair & Accessories

Connector Type Search

- 0 +
☐

- 0 +
☐

- 0 +
☐

- 0 +
☐

- 0 +
☐

- 0 +
☐

Add to Cart Inquiry

Specifications	Download / CAD
Nominal Current N/A	Connector Type Waterproof Cap
Shielded Metal, Non-shielded	No. of Contacts N/A
Connector Gender Male	Backshell N/A
Mating Style Screw Thread	IP Rating N/A
Assembly Style N/A	
+ More Options	

People Also Bought

- 

CAP-WBDM SMA2
- 

MSAS-08BMMM-...
- 

MSAP08MR-SAPMR...
- 

SSL12-J4FJ0-000001
- 

1BB-028FMM-LL7A10