

Enhanced Eurocard packaging: Card Frame Components



CARD GUIDES - SINGLE

Ordering information


Card Guide-Single. (2 required per slot.)

	Model Number		
	Black	Tan	Red
(single)	61310-01-B	61310-01-NB	61310-01-R
(single, half length)			
"ABC" half	61311-01-B	61311-01-NB	61311-01-R
"DEF" half	61311-02-B	61311-02-NB	1311-02-R

NOTE: Other sizes available



Single Card Guides




Card guide specifications

Material:	nylon, black only, 25% glass filled
Specification:	UL Yellow card #E43392(N) UL flammability Rate: 94V-0
Standards:	ASTM D-4066

ESD CLIPS

Ordering information

ESD Clips	Model Number
ESD Clip - Card Guide. Mounted in the front of the card guide for PCB ESD discharge.	
(each)	61317-01
(Sold in sets of 25)	ESD-CG
ESD Clip - Alignment Pin. Located in the alignment pin mounting hole in front of card guide.	
(each)	61318-01
(Sold in sets of 25)	ESD-AP



ESD Clips, right (shown inserted in guides on left)

ESD clip specifications

Material:	BeCu Alloy 25, 1/4 hard, 0.012 thick (ESD-CG/61317-01) BeCu Alloy 25, 1/4 hard, 0.008 thick (ESD-AP/61318-01)
Finish:	Sulfamate Nickel per MIL-P-27418, matte texture

Enhanced Eurocard packaging: Card Frame Components

UNIT PROGRAMMING KEYS


Unit Programming Key ordering information –

Sold in sets of 12.

Color	Model Number
Black	PK-B
Tan	PK-NB
Red	PK-R

Unit Programming Key specifications

Material:	nylon, black only, 25% glass filled
Specification:	UL Yellow card #E43392(N) UL flammability Rate: 94V-0
Standards:	ASTM D-4066




Unit Programming Keys

END PLATES

Ordering information

(2 required per frame)

Model Number				
3U	6U	9U	Extension:	Style
61350-160	61351-160	61352-160	None	1101.10
61355-161	61356-161	61357-161	160 + 80	1101.11
61355-162	61356-162	61357-162	160 + 100	1101.11
61355-163	61356-163	61357-163	160 + 120	1101.11
61355-164	61356-164	61357-164	160 + 140	1101.11
61355-165	61356-165	61357-165	160 + 160	1101.11



End Plates

HORIZONTAL RACK MOUNTING FLANGES

Horizontal Rack mounting Flanges

No of slots	6U		9U		Mounting Bar
	Left	Right	Left	Right	
6	61054-11	61054-13	61054-11	61054-12	61052-11
8	61054-14	61054-16	61054-14	61054-15	61052-12
10	61054-17	61054-19	61054-17	61054-18	61052-13

See "Card Cage Drawings" in Eurocard Packaging Products Section

EMC GASKETS

fits bars 61360 thru 61368, Dot•Ten Eurocard Front Panels and Dot•Ten filler panel

	3U	6U	9U	Size/Style:
Model Number	61316-01	61316-03	61316-05	Front Panel
Dimension	4.000(101,60)	9.000(228,60)	14.250(361,95)	
Model Number	61316-02	61316-04	61316-06	Filler Panel
Dimension	4.250(107,95)	9.500(241,30)	14.750(374,65)	



EMC gasket

EMC Gasket specifications

Material:	BeCu Alloy 25
Finish:	Nickel, bright QQ-N-290