


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE
PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE
WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.


REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
B	ECN 11696: ADD RATING TEMPERATURE NOTE	2/21/22	DGUST



DIMENSIONS
ARE
METRIC

PART NUMBER	LENGTH METER [FEET]
DPA00006-05M	.5 [1.64]
DPA00006-1M	1.0 [3.28]
DPA00006-2M	2.0 [6.56]
DPA00006-3M	3.0 [9.84]

PIN OUT




NOTES:

CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
NO OPENS/SHORTS, MISWIRING OR INTERMITTENT FAILURES.

VOLTAGE TEST: DC 300V 10MS
INSULATION RESISTANCE: 5.0M OHM / MIN.
CONDUCTOR RESISTANCE: 5.0 OHM / MAX.
RATING: TEMPERATURE 80°C

CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
CE2011/65/EU (RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]		APPROVALS		DATE		 an INFINITO™ brand		750 High Street, West Mill, North Andover, MA 01845 USA Phone: 1.800.341.5266 1.978.682.6936					
OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0		DRAWN BY B.PUCHAASKI		05/21/18		CATEGORY		AUDIO VIDEO					
		CHECKED BY J.LABOY		05/21/18									
		APPROVED BY B.GATES		05/21/18									
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS .XX = ± .02 [.5] ± 1/32 .XXX = ± .005 [.13] ANGLES ± 1°		CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY				PRODUCT DESCRIPTION DISPLAYPORT CABLE 20 PIN							
THIRD-ANGLE PROJECTION 		COLOR VARIATIONS MAY OCCUR				SIZE A		CAGE CODE 43321		ITEM NO. DISPLAYPORT CABLE 20 PIN		REV B	
						SCALE: NONE		CAD FILE: DPA00006.SLDRW				SHEET 1 OF	