





1.Wiring Diagram.



2.Cable test condition :

Open / Short : 100%

Insulation resistance : 5M ohms

Contact resistance : 2 ohm

Hipot : DC 300V / 1 sec

3.Each pcs with PE polybag.

7	COPPER	COPPER FOIL 20X40MM	1		B	20001	ADD COPPER FOIL	2020/05/07
6	COPPER	COPPER FOIL 15X40MM	1		A		INITIAL RELEASE	2014/08/28
5	CONN	USB3.0 MICRO B MALE G/F BLACK	1	P2	REVIEW#		DESCRIPTION	DATE
4	PVC	45P PVC BLACK OVERMOLD	25g		P/N:		103-1092-BL-00100	REV B
3	PE	LLDPE 500026 6201	16g		TITLE		CABLE USB3.0 A/M TO MICRO B MALE	
2	CONN	USB3.0 A/M G/F BLUE	1	P1	DRAWN	WENC	DATE	08/24/14
1	CABLE	《28AWG (7/0.12TC) *1P+D(7/0.10TC)+AL+M》*2+28AWG (7/0.12TC) *1P+24AWG(7/0.2TC)*2C+A+D+B (96/0.12AM) OD5.5 BLACK	1	1000mm	CHECKED	EDWIN	DATE	08/24/14
NO.	PART NO.	DESCRIPTION	QTY	UNIT/REF	APPROVAL		SHEET	1 OF 1

BILL OF MATERIAL

CnC Tech,LLC

103-1092-BL-00100

CABLE USB3.0 A/M TO MICRO B MALE

CUSTOMER P/N:

REV B

CUSTOMER:

SHEET 1 OF 1

APPROVAL

SHEET

1 OF 1

Downloaded from Arrow.com