

[Products](#)[Customize Your Parts](#)[Industries Solutions](#)[Search](#)[News & Events](#)[First Time?](#)

[Home](#) / [Products](#) / [M Series](#) / [M12 \(X\)](#)

## Product Line

Single Pair Ethernet >

ZConnect >

Ceres >

X-Lok >

M Series >

Accessory

M5

Guided M8

M8

M10.5

M12 (A)

M12 (B)

M12 (D)

M12 (I)

M12 (K)

M12 (L)

M12 (S)

M12 (T)

M12 (X)

M23

FLOS & FLOS+ >

Power >

RBL >

HS-Lok >

NMEA 2000 >

Heavy Duty Shielded >

RJ >

USB >

SSL >

HDMI >

DVI >

Fiber Optic >

RF >

Cable Joiner >

Cable Gland >

Pressure Relief Vent >

LED Light Guide >

D-Sub >



## MSXS-08PFFR-SH7002

Operating Temperature: -40°C ~ +105°C

Transmission Speed: N/A

Shielded: Metal, Shielded

Jacket Material: N/A

Certificate: UL1863

You must login first for view the price


Quantity 

- 1 +

Check Stock

Add to Cart

Inquiry



Can't find? [Customize your part](#)

## Mating Pair & Accessories

Connector Type

Search

M Series, M12, X Code, APPM-A08MAPAS-XS1  
-40°C ~ +105°C

M Series, Accessory, CAP-WBDFSMA1  
-40°C ~ +105°C

M Series, Accessory, CAP-WBDFSMA2  
-40°C ~ +105°C

M Series, Accessory, CAP-WBDFSPB1  
-40°C ~ +105°C

| Specifications                      | Download / CAD                      |
|-------------------------------------|-------------------------------------|
| Nominal Current<br><b>0.5A</b>      | Connector Type<br><b>Receptacle</b> |
| Shielded<br><b>Metal, Shielded</b>  | No. of Contacts<br><b>08</b>        |
| Connector Gender<br><b>Female</b>   | Backshell<br><b>Hexagonal</b>       |
| Mating Style<br><b>Screw Thread</b> | IP Rating<br><b>IPX7</b>            |
| Assembly Style<br><b>PCB 90°</b>    |                                     |
| <div> More Options</div>            |                                     |

### People Also Bought

