










APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	01/17/07	
A		UPDATED DRAWING	2/13/17	HR/CH
B		UPDATED DRAWING	7/29/19	LH/NL



SPECIFICATIONS:

Material:
Insulator: Hi-temp thermoplastic, rated UL 94V-0
Insulator color: Nature
Contacts: Brass, Tin plated
Solder nail: Brass

Electrical:

Current rating: 1A AC/DC
Contact resistance: 20 mohms max
Insulation resistance: 100 Mohms min
Withstanding voltage: 250 VAC for 1 minute

Temperature Rating:

Operating temperature: -40°C to +85°C
Environmental:
Lead free, RoHS compliant



PACKAGED ON TAPE & REEL

Positions: 2 thru 15

A= .049 [1.25] x No. of Spaces

B= .049 [1.25] x No. of Spaces +.118 [3.00]

C= .049 [1.25] x No. of Spaces +.071 [1.80]

D= .049 [1.25] x No. of Spaces +.252 [6.40]

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED

INCHES	HOLES
.X ±.10	Ø.X ±.10
.XX ±.020	Ø.XX ±.015
.XXX ±.015	Ø.XXX ±.010

APPROVALS		DATE
DRAWN	BW	01/17/07
CHECKED		
APPROVED		

ADAM
TECH
INTERCONNECTS

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE
.049 [1.25] PITCH WIRE TO BOARD HEADER
STRAIGHT, SMT TYPE

SIZE X	PART NO. 125SH-B-XX-TS-SMT-T/R	REV. B
REF: S00124T	SCALE: NTS	SHEET 1 OF 1