


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE
PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE
WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	12/08/03	B.MAZE/JKA
B	ECN 3196: UPDATE DWG FORMAT	2/13/08	D.GRIFFIN
C	ECN3680, ADDED PACKAGING TABLE	2008.10.30	E. STAUBLE
C	ECN99999:REMOVED PACKAGE IN POLYBAG NOTE	11/10/08	D.GRIFFIN



NOTES:

MATERIAL:

SHELL: STEEL

INSULATOR: PBT W/GLASS FIBER FILL (UL 94V-0 RATED)

FINISH:

FRONT SHELL: BRIGHT TIN/NICKEL PLATED

REAR SHELL: BRIGHT TIN PLATED

CATALOG #	PACKAGING
C&P37F	1/BAG
C&P37F-TRAY	40/TRAY

RoHS Compliant ✓

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]		APPROVALS		DATE		L-com CONNECTIVITY PRODUCTS		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] -60 [1524] = +2 [51] / -0 >60 [1524] -120 [3048] = +4 [102] / -0 >120 [3048] -300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%		DRAWN BY B.MAZEJKA		11/10/2003		CATEGORY DSUB			
		CHECKED BY C.McCORMICK		12/08/2003					
		APPROVED BY D.PARHAM		12/08/2003					
ALL OTHER DIMENSIONAL TOLERANCES: .X = .3 .XX = .15		CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY				PRODUCT DESCRIPTION DB37F PIN CRIMP & POKE CONNECTOR			
		PROJECTION 		COLOR VARIATIONS MAY OCCUR		SIZE A	FSCM NO. 43321	DWG. NO. C&P37F	REV C
		REF		SCALE: NONE CAD FILE: C&P37F.SLDRW				SHEET 1 OF	